



Fork joint GN 751



Rostfrei
Inox
Stainless
Steel

3.1

3.2

3.3

3.4

1

2

d ₁ H9	d ₂	d ₃	d ₄	Length l	r	s -0,2	t Min.	w Min.
6	M 6	10	14	22	8,5	6	12	218°
8	M 8	14	18	29	12	8	16	218°
10	M 10	18	23	35	14	10	20	212°
12	M 12	20	27	43	17	12	24	216°
14	M 14	24	30	50	19	14	28	214°
16	M 16	26	36	56	22	16	32	216°

3.5

3.6

Specification

- Steel
 - Property class 5
 - Zinc plated, blue passivated
- Stainless steel AISI 303 **NI**
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166
- RoHS

3

Information

Joints pieces GN 752 are designed to be used in combination with fork heads DIN 71752 respectively fork joints GN 751.

see also...

- Swing Nuts GN 444.2 → Page 1079
- Fork Head DIN 71752 → Page 1662 ff.
- Fork Joints GN 751 → Page 1662 ff.

3.7

3.8

3.9

How to order (Steel)	1	d ₁
GN 752-10-M10	2	d ₂

How to order (Stainless Steel)	1	d ₁
GN 752-8-M8-NI	2	d ₂
	3	Material

