



- 4 Type**
- A** Without pin
  - KL** Pin with KL retaining clip
  - SL** Pin with SL retaining clip

<b>1</b> $d_1$ H9/h11	<b>2</b> $l_1$	<b>3</b> $d_2$	$a$	$b$	$l_2$	$l_3$	$l_4$	$l_5$ min.
6	12	M 6	12	6	37	44	20	15
8	16	M 8	16	8	47	57	25	20
10	20	M 10	20	10	57	69	30	25
12	24	M 12	24	12	68	82	35	30
14	28	M 14	27	14	78	94	40	35
16	32	M 16	32	16	89	108	45	40

**Specification**

**Fork head**

Steel  
Zinc plated, blue passivated

**ST**

**Pin for type KL / SL**

Steel  
Zinc plated, blue passivated

**Retaining clip for type KL / SL**

Spring steel  
• Hardened and tempered  
• Zinc plated, blue passivated

RoHS

**On request**

• Stainless steel

Fork heads GN 754 transmit tensile and shearing forces, such as from rods, levers or cable pulls. The length of the external thread enables a significantly larger adjusting range than fork heads with internal thread.

The versions with pins can be combined with brackets or joint pieces GN 752 to create fork joints, which can be quickly and easily assembled and disassembled without tools, especially with type KL.

Fork heads GN 754 are dimensioned according to DIN 71752.

**see also...**

**GN 751 | DIN 71752 Fork Heads (with Internal Thread)** **Page**  
QVX

**Technical Information**

ISO Fundamental Tolerances QVX

**Accessory**

**GN 752 Joint Pieces** QVX

**How to order**

<b>1</b>	$d_1$
<b>2</b>	$l_1$
<b>3</b>	$d_2$
<b>4</b>	Type
<b>5</b>	Material

**GN 754-10-20-M10-SL-ST**