


Application examples



1 s	2 l ₁	d	l ₂	l ₃
∅ Linear actuators				
30	22	M 4	32	23
50	30	M 5	50	31

Specification

Adjustable hand lever

- Handle
 - Zinc die casting
 - Powder coated
 - Orange, RAL 2004, textured finish ● OS
- Insert / Retaining screw
 - Stainless steel AISI 303

Clamping wedges

Brass

RoHS

Carriage clamping units GN 891.3 secure carriages of configurable profile linear actuators without tools once they have been positioned. This prevents unintentional movement, e.g. due to vibrations or accidental operation. The thread of the adjustable hand lever clamps the wedge mechanism. The resulting friction between the clamping wedges and the carriage guideway secures the carriage position efficiently and without backlash.

see also...	Page
GN 8910 Profile Linear Actuators (with One Carriage)	QVX
GN 8920 Profile Linear Actuators (with Two Opposing Carriages)	QVX

Technical Information

Stainless Steel Characteristics	Page
	QVX

How to order

GN 891.3-50-30-OS

1	s
2	l ₁
3	Color