



**elesa**

Original design ETH-EP/-AN



IF product design award



reddot design award winner

1 2

d <sub>1</sub>	l <sub>1</sub> ±1					a	b	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	
28	300	400	500	600	700	-	62,5	28	10,5	54	68	20	26	19,5	20,3
35	300	400	500	600	700	1000	74	35	10,5	67,5	85	28	24,5	28,5	18,5

**Specification**

**Handle tube**

Aluminum, wall thickness 2 mm

**GN 767**

**Tube**

Powder coated

Graphite black, metal effect, matte finish

**GN 767.1**

**Tube**

Anodized, natural color

**End caps**

Plastic, Polyamide (PA)

- Black-gray, RAL 7021, shiny finish
- Orange, RAL 2004, shiny finish
- Gray, RAL 7035, shiny finish
- Yellow, RAL 1021, shiny finish
- Blue, RAL 5024, shiny finish
- Red, RAL 3000, shiny finish
- Green, RAL 6017, shiny finish

- **DSG**
- **DOR**
- **DGR**
- **DGB**
- **DBL**
- **DRT**
- **DGN**

**End pieces**

Plastic, Polyamide (PA)

- Glass fiber reinforced
- Operating temperature -20 °C to +100 °C
- Black-gray, matte finish, similar to RAL 7021

RoHS

**On request**

Tube and end pieces / end caps in white (WS)

The design of the cabinet U-handles GN 767 / GN 767.1 matches the product family Ergostyle®.

The mechanism (screws and nuts) is shrouded by the removable end caps. Available in the different Ergostyle® colors they offer additional possibilities for color schemes.

On assembly the two end caps are inserted from above. To remove the end caps, a flat screw driver is used in the recess to prise them out of their location.

see also...	Page
<b>GN 667</b> Cabinet U-Handles (Mounting from the Operator's Side)	QVX

**Technical Information**

Product Family Ergostyle®	QVX
Strength Properties	QVX
Load Rating Information	QVX
Plastic Characteristics	QVX

**How to order (Tube Powder Coated)**

1	d <sub>1</sub>
2	l <sub>1</sub>
3	Color (End caps)

**GN 767-35-700-DSG**

**How to order (Tube Anodized)**

1	d <sub>1</sub>
2	l <sub>1</sub>
3	Color (End caps)

**GN 767.1-35-500-DSG**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

