


Mounting example



3.1

3.2

3.3

3.4

1 2

b Size of the slide	l ₁	d Socket cap screws DIN 912	h ₁	h ₂	h ₃	l ₂	s
30	41	M 2,5	18,4	10	4,2	35,4	6
50	67	M 3	28	14	7	58	9
80	105	M 4	39	14	12,5	92	9
120	145	M 5	47,6	20	13,8	131,8	12

3.5

3.6

Specification

- Aluminum
Anodized, natural color
- Socket cap screws DIN 912
Stainless steel
- RoHS

Information

Rotary plates GN 900.5 allow rotation of one of the adjustable slide units at an offset angle to the other. This offers an additional possible axis configuration.

The alternative adaptor consists of two plates connected together in the center so they may be rotated. The lower plate is clamped to the lower sliding part, while the upper one is clamped to the stationary base of the upper sliding unit.

All parts required are included.

see also...

- Adjustable Slide Units GN 900 → Page 1938

3.7

3.8

How to order	1 b
GN 900.5-80-105	2 l ₁

