



2

3

d <sub>1</sub>	d <sub>2</sub>			d <sub>3</sub>	d <sub>4</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub> ≈	l <sub>4</sub>
16	M 6	-	-	10	13	41,5	12	2,5	15
18	M 6	M 8	-	10	14,5	56	13	2,5	19
22	M 6	M 8	M 10	14	18,5	59	14	2,5	21
24	M 8	M 10	-	14	18,5	74	16	2,5	27
25	M 10	-	-	16	20	84	16	2,5	30

**Specification**

- Plastic Technopolymer (Polyamide PA)
  - Temperature resistant up to 90 °C
  - Black, matte finish
- Aluminum Polished
- Spindle Steel
  - Zinc plated, blue passivated
- *Plastic Characteristics* → Page 2158
- RoHS

1

**KT**

**AL**

**Information**

Typical in design are the revolving handles GN 798 with their stepped shape consisting of two cylinders giving the operator a better grip.

see also...

- *Revolving Handles GN 798.2 (with Internal Thread)* → Page 35
- *Retractable Handles GN 798.3 (with Hold in Both Positions)* → Page 52
- *Safety Retractable Handles GN 798.7 (Automatic Return to the Retracted Position)* → Page 53

How to order

**GN 798-KT-24-M10**

1	Material
2	d <sub>1</sub>
3	d <sub>2</sub>