




3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8



d <sub>1</sub>	Rotating range	Concentricity tolerance	Circular runout tolerance	max. entry torque M <sub>D</sub> in Nm	max. load capacity of rotary disk		F max. in N
					unclamped in Nm	clamped M <sub>K</sub> in Nm	
55	0°... ∞	±0,02	±0,02	1,5	5	10	50
80	0°... ∞	±0,03	±0,03	2,5	5	10	100

3.9

