



**3** Type  
**A** Without thread coating  
**GPC** With micro encapsulation

**2**

d				h	A/F
Steel ST	Stainless steel NI / A4				
M 6 x 1	-	-	-	6	3
M 8 x 1	-	M 8 x 1	-	8	4
M 10 x 1	R 1/6	M 10 x 1	R 1/6	8	5
M 12 x 1,5	-	M 12 x 1,5	-	10	6
M 14 x 1,5	R 1/4	M 14 x 1,5	R 1/4	10	7
M 16 x 1,5	-	M 16 x 1,5	-	10	8
M 18 x 1,5	R 3/6	M 18 x 1,5	R 3/6	10	8
M 20 x 1,5	R 1/2	M 20 x 1,5	R 1/2	10	10
M 22 x 1,5	-	M 22 x 1,5	-	10	10
M 24 x 1,5	-	M 24 x 1,5	-	12	12
M 26 x 1,5	R 3/4	-	R 3/4	12	12
M 30 x 1,5	R 1	-	R 1	12	17
M 36 x 1,5	-	-	-	15	19
M 42 x 1,5	R 1 1/4	-	-	18	22
M 45 x 1,5	-	-	-	18	22
M 48 x 1,5	R 1 1/2	-	-	20	24

**Specification**

<b>Steel</b>	<b>ST</b>
Zinc plated, blue passivated	
<b>Stainless steel</b> AISI 303	<b>NI</b>
<b>Stainless steel</b> AISI 316Ti	<b>A4</b>
<b>Thread coating</b> for type GPC	
Precote 5	
• White	
• Operating temperature -60 °C to +150 °C	

RoHS

Threaded plugs DIN 906 are used to close bore holes with cylindrical internal thread.

The tightness depends on the medium, pressure, temperature and material pairing. The type GPC with thread coating provides a higher degree of safety.

see also...

	Page
<b>GN 749</b> Threaded Plugs (Steel)	QVX
<b>DIN 908</b> Threaded Plugs (Steel)	QVX
<b>DIN 910</b> Threaded Plugs (with Collar and External Hex)	QVX

**Technical Information**

Thread coating GPC	QVX
Stainless Steel Characteristics	QVX

How to order

<b>1</b> Material
<b>2</b> d
<b>3</b> Type

**DIN 906-ST-M36x1,5-GPC**

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10