



2

d_1	d_2	d_3	$l_1 \approx$	l_2	l_3	$l_4 \approx$	l_5	l_6
16	M 5	16	58	15	5	52,5	9,5	5
18	M 5	16	72,5	15	5	67	9,5	5
22	M 6	20	80,5	19,5	6	74	10,5	7
24	M 6	20	95,5	19,5	6	89	10,5	7
25	M 6	20	105,5	19,5	6	98,5	10,5	7

Specification

Handle

- Plastic, Polyamide (PA)
- Operating temperature up to 90 °C
- Black, matte finish
- Revolving

1

KT

GN 798.3

Retractable mechanism

Steel, blackened

GN 798.5

Retractable mechanism

- Stainless steel
- Spindle, AISI 303
- Flat base, AISI 316LHC, sintered

RoHS

The design of the retractable handles GN 798.3 / GN 798.5 is characterized by their shape, consisting of two cylinders. It gives the hand an excellent grip, especially because the handle has to be pulled out of the locked position to fold it over.

Retractable handles GN 798.3 / GN 798.5 are used when the handle should not protrude temporarily for space or safety reasons.

see also...

	Page
GN 598.3 Retractable Handles (Retractable Mechanism Steel, Locked in Operating Position)	QVX
GN 598.5 Retractable Handles (Retractable Mechanism Stainless Steel, Locked in Operating Position)	QVX

Technical Information

	Page
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order (Steel)

GN 798.3-KT-22

- 1 Material
- 2 d_1

How to order (Stainless Steel)

GN 798.5-KT-25

- 1 Material
- 2 d_1