Threaded Plugs

Steel / Stainless Steel, with Collar, with Internal Hex





STAINLESS ★★★★

3 Type

A	Without sealing ring
AC	With sealing ring in copper
AA	With sealing ring in aluminum
AN	With sealing ring in stainless steel

2

d_1 Steel ST	d_1 Stainless steel A4	d_2 h14	d_3	d_4 Sealing Outside diameter	l_1 ±0,2	l_2 +0,5	s	A/F
M 8 x 1	M 8 x 1	12	8,3	11,5	8	3	1	4
M 10 x 1	M 10 x 1	14	10,3	13,5	8	3	1	5
M 12 x 1,5	M 12 x 1,5	17	12,3	16	12	3	1,5	6
M 14 x 1,5	M 14 x 1,5	19	14,3	18	12	3	1,5	6
M 16 x 1,5	M 16 x 1,5	21	16,3	20	12	3	1,5	8
M 18 x 1,5	M 18 x 1,5	23	18,3	22	12	4	1,5	8
M 20 x 1,5	M 20 x 1,5	25	20,3	24	14	4	1,5	10
M 22 x 1,5	M 22 x 1,5	27	22,3	27	14	4	1,5	10
M 24 x 1,5	M 24 x 1,5	29	24,3	29	14	4	2	12
M 26 x 1,5	-	31	26,3	31	16	4	2	12
M 27 x 2	-	32	27,3	32	16	4	2	12
M 30 x 1,5	-	36	30,3	36	16	4	2	17
M 33 x 2	-	39	33,3	39	16	5	2	17
M 42 x 2	-	49	42,3	49	16	5	2	22
M 48 x 2	-	55	48,3	55	16	5	2	24
G 1/8	G 1/8	14	10	13,5	8	3	1	5
G 1/4	G 1/4	18	13,4	18	12	3	1,5	6
G 3/8	G 3/8	22	17	21	12	3	1,5	8
G 1/2	G 1/2	26	21,3	26	14	4	1,5	10
G 3/4	G 3/4	32	26,7	32	16	4	2	12
G 1	G 1	39	33,5	39	16	5	2	17
G 1 1/4	G 1 1/4	49	42,2	49	16	5	2	22
G 1 1/2	G 1 1/2	55	48,1	55	16	5	2	24

Specification

1

Threaded plug

- Steel **ST**
  - Zinc plated, blue passivated
  - Property class 5.8
- Stainless steel AISI 316 / AISI 316Ti **A4**

Sealing ring DIN 7603

- Copper for type AC
- Aluminum for type AA
- Stainless steel for type AN

RoHS

Technical Information	Page
ISO Fundamental Tolerances	QVX
Strength Values of Screws	QVX

Threaded plugs DIN 908 are used, for example, on filling, drain or inspection openings of gear boxes and hydraulic tanks.

see also...	Page
GN 746 Threaded Plugs (Plastic)	QVX
GN 749 Threaded Plugs (with Rubber Sealing)	QVX
DIN 910 Threaded Plugs (with External Hex)	QVX

Accessory

DIN 7603 Sealing Rings	QVX

How to order

DIN 908-ST-M24x1,5-AN (1 2 3)

1	Material
2	d_1
3	Type