



d ₁		d ₂	d ₃	d ₄	l ₁	l ₂	l ₃ ≈	l ₄	s
KT	NI								
16	-	M 6	10	13	41,5	12	4	15	8
18	18	M 6	10	14,5	56	13	4	19	8
22	22	M 8	14	18,5	59	14	5,2	21	11
24	24	M 10	14	18,5	74	16	5,2	27	11
25	-	M 10	16	20	84	16	5,5	30	13

Specification

Handle

- Plastic Polyamide (PA)
- Operating temperature up to 90 °C
- Black, matte finish
- Stainless steel AISI 303
- Fine turned, plain



KT

NI

Spindle

Stainless steel AISI 303

RoHS

Typical in design are the revolving handles GN 798.4 with their stepped shape consisting of two cylinders giving the operator a better grip.

see also...

GN 798.5 Retractable Handles (with hold in both positions) Page QVX

Technical Information

Plastic Characteristics QVX

Stainless Steel Characteristics QVX

How to order	1	Material
GN 798.4-KT-16-M6	2	d ₁
	3	d ₂