



ROSTFREI
Inox
Stainless
Steel

1 **2** **3** Hand lever with threaded stud

| l_1 | d_1 | l_2 | d_2 | h_1 | $h_2 \approx$ |
|-------|-------|-------|-------|-------|---------------|
| 45 | M 6 | 20 | 10 | 9 | 34 |
| 63 | M 6 | 20 | 10 | 12 | 44 |

1 **2** Hand lever with threaded bushing

| l_1 | d_3 | l_2 | d_2 | h_1 | $h_2 \approx$ |
|-------|-------|-------|-------|-------|---------------|
| 63 | M 8 | - | - | - | 45 |
| 78 | M 8 | - | - | - | 54 |
| 78 | M 10 | - | - | - | 54 |
| 92 | M 10 | - | - | - | 64 |

Specification

- Handle
Stainless steel
Precision casting AISI CF-8
Matte shot-blasted **GS**
- Bushing / Threaded insert
Stainless steel AISI 303
- Retaining screw
Stainless steel AISI 303
- Pressure spring
Stainless steel AISI 301
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

Adjustable hand levers GN 911.3 replace the socket cap screws DIN 912 or the cap nuts DIN 917 of the tube clamp connectors and linear actuator connectors in stainless steel.

The table of dimensions of the tube clamp connectors and linear actuator connectors shows the matching hand lever for each screw location.

| | | |
|---------------------------------|---|--------|
| How to order (Threaded bushing) | 1 | l_1 |
| GN 911.3-63-M8-GS | 2 | d_3 |
| | 4 | Finish |

| | | |
|------------------------------|---|--------|
| How to order (Threaded stud) | 1 | l_1 |
| GN 911.3-45-M6-20-GS | 2 | d_1 |
| | 3 | l_2 |
| | 4 | Finish |

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

