



2

d ₁	d ₂	d ₃	l ₁ ≈ (arrested)	l ₂	l ₃	l ₄	l ₅	l ₆
22	M 6	20	82	22	5,5	73	13	7
24	M 6	20	97	22	5,5	88	13	7
25	M 6	20	107	22	5,5	98	13	7

Specification

Handle

- Plastic, Polyamide (PA)
- Operating temperature up to 90 °C
- Black, matte finish
- Revolving

1

KT

GN 798.7

Retractable mechanism

- Steel
- Spindle 1.0718 Blackened
- Flat base Sintered, blackened

GN 798.8

Retractable mechanism

- Stainless steel
- Spindle, AISI 303
- Flat base, AISI 316LHC, sintered

RoHS

Safety retractable handles GN 798.7 / GN 798.8 are suitable for applications such as cranked handles and handwheels if the handle may not be locked in the operating position.

In order to bring the handle into the operating position it has to be turned first through 90° to a stop against a torsion spring and then it is pushed against spring pressure into its hold position.

Operated in this way and with the axial force maintained, the handle can be used to crank.

When „releasing“ the handle, the pressure spring returns it back to the retracted position.

Technical Information

	Page
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order (Steel)

GN 798.7-KT-24

1	Material
2	d ₁

How to order (Stainless steel)

GN 798.8-KT-25

1	Material
2	d ₁