


Application example



m	h ₁	a	b ₁	b ₂	d ₁	d ₂	h ₂ ≈	h ₃	h ₄	Length l	For toggle clamps			
											GN 810 GN 810.1 GN 810.3 GN 810.4	GN 820 GN 820.1 GN 820.2 GN 820.3 GN 820.4	GN 860	GN 842
85	16	12,5	11,5	15	6,2	M 6	5,7	12	37	100	130	130	125	70
100	18	15	14	18	8,2	M 8	6,3	15,5	43	120	230	230	200	360

Specification

- Steel
 - Zinc plated, blue passivated
 - RoHS
- ST

Information

Clamping arm extenders GN 801.1 are used together with toggle clamps with “forked clamping arm” to clamp something simultaneously at two points in parallel, such as with clamping screws. These are mounted to the clamping arm and affixed in the desired position along the slot.

The side position of the clamping screws can also be selected via the slots, a symmetrical arrangement/setting encourages a balanced clamping result.

All parts are supplied in a non-assembled set. Four flanged washers are included for fastening the clamping screw.

- see also...
- Clamping Arm Extenders GN 801.2 (with Joint) → Page 817
 - Clamping Arm Extenders GN 809.1 → Page 819
 - Clamping Screws GN 804 → Page 810
 - Clamping Screws GN 807 → Page 811

How to order	1	m
	2	h ₁
	3	Material
GN801.1-85-16-ST		