



2 Type

- A** Without screw / threaded bushing
- B** With threaded bushing



d ₁	d ₂	d ₃	d ₄	h ₁	h ₂	A/F	t ₁	t ₂	t ₃ min.
11*	M 4	5,5	8,2	6,5	-	-	1	4	-
12	M 5	7	9,3	8	11	10	1,5	5,3	6
15	M 6	8,5	11,5	10	14	12	2	6	7
19	M 8	11	15	13	18	16	2	7,5	8,5
24	M 10	13	20	16	23,5	21	2,2	9,2	10
26	M 12	16	22	19	26	22	2,5	10,5	12

* Protective caps d₁ = 11 are only available in type A (without screw / threaded bushing)

Specification

- Rubber (CR)
 - Hardness 85±5 Shore A
 - Black
- Threaded bushing
 - Steel
 - Zinc plated, blue passivated
- *Elastomer Characteristics* → Page 2158
- **RoHS**

Information

Protective caps GN 806 can be used with hexagon screws ISO 4017 or together with threaded pins type B as thrust pins with soft clamping head surface, or as soft end stop bolts.

A typical application is in conjunction with toggle clamps (product group 2.4).

see also...

- *Buffers GN 352 / GN 452* → Page 1531
- *Buffers GN 353 / GN 453* → Page 1526 / 1527

How to order

GN 806-24-B

1 d₁

2 Type

3.1

3.2

3.3

3.4

3.5

3.6

3.7

3.8

3.9

