



1 l <sub>1</sub>	2 l <sub>2</sub>	3 d <sub>1</sub>	a		Type RF max.	min.	b	d <sub>2</sub> Ø	h <sub>1</sub> ≈	h <sub>2</sub>	l <sub>3</sub> max.	For wedge clamps GN 920.1 with:	
			Type GA / max.	Type GL min.								d	b
25	32	M 8	44,5	39,5	39,5	34,5	21	18	27,5	4	7,5	M 8	21
29	32	M 8	44,5	39,5	39,5	34,5	25	18	27,5	4	7,5	M 8	25
36	32	M 8	44,5	39,5	39,5	34,5	32	18	27,5	4	7,5	M 8	32
44	32	M 8	44,5	39,5	39,5	34,5	40	18	27,5	4	7,5	M 8	40
44	32	M 12	45,5	40	45,5	40	40	23	38	5	11,5	M 12	40
54	32	M 8	44,5	39,5	39,5	34,5	50	18	27,5	4	7,5	M 8	50
54	32	M 12	45,5	40	45,5	40	50	23	38	5	11,5	M 12	50

**Specification**

**Plate**

Steel  
Blackened

**Socket cap screw ISO 4762**

Steel

**Distance sleeve**

Steel

RoHS

Pull-down plates GN 920.2 allow wedge clamps GN 920.1 to clamp easily with pull-down effect.

The socket cap screw ISO 4762 and the distance sleeve are included.

see also...

GN 920.1 Wedge Clamps

Page

QVX

How to order

**GN 920.2-36-32-M8**

- 1 l<sub>1</sub>
- 2 l<sub>2</sub>
- 3 d<sub>1</sub>

