



reddit design award
winner

2 Bore code

B Without keyway

K With keyway DIN 6885-1 P9

4 Type

A Without handle

R With revolving handle

1

3

d ₁	d ₂ H7 Bore		d ₃	d ₄	b	h	l ₁	l ₂ ≈	l ₃ ≈	r	Ø Handle GN 798.2	Recommended countersunk washer
125	12	14	31	23	15	11	18	33,5	61,5	45,5	22	GN 184-20
140	14	16	36	28,5	16,5	13	19	36,5	76,5	52	24	GN 184-25
160	14	16	36	28,5	18	14,5	20	39,5	76,5	61	24	GN 184-25
200	18	20	42	36	20,5	16	24	45,5	85	77,5	25	GN 184-32

Specification

5

Wheel body

Aluminum die casting

- Hub machined
- Rim turned
- Radial and axial runout < 0.4

• Powder coated

- Black, RAL 9005, textured finish
- Silver, RAL 9006, textured finish

● **SW**
○ **SR**

Cover

Plastic, Polyamide (PA)

Light grey

Revolving handle GN 798.2

Plastic, Polyamide (PA)

- Black, matte finish
- Spindle steel
- Zinc plated, blue passivated

RoHS

Spoked handwheels GN 924 are distinguished by modern design.

The removable plastic cover shrouds the fixing components such as countersunk washers and protruding or recessed shafts.

see also...

GN 322 Spoked Handwheels (Aluminium, Rim Polished)

Page

QVX

Technical Information

Keyway P9 DIN 6885-1

Cross holes GN 110

ISO Fundamental Tolerances

QVX

QVX

QVX

Accessory

GN 184 Countersunk Washers (for Axial Fastening)

QVX

How to order

1 d₁

2 Bore code

3 d₂

4 Type

5 Color

GN 924-125-K12-A-SR