

GN 80i

Transport and Base Plates

Zinc Die Casting, for Aluminum Profiles (i-Modular System)







4.8

S ര്

3.6

3.7

လ က

3.9

Ų	2	ą	4							
s ₁	S ₂	n	d ₁		d ₂ For screw	h ₁	h ₂	m ₁	m ₂	Grid size
30	60	6	M 8	M 10	M 6	12	5	30	-	30
40	80	8	M 10	M 12	M 8	16	6,5	40	-	40
60	60	6	M 10	M 12	M 6	12	5	30	30	30
80	80	8	M 12	M 16	M 8	16	6,5	40	40	40

Spe	ecifi	cation
-----	-------	--------

· Zinc die casting, black RoHS

Accessory

T-Nuts GN 50i → Page QVX

Information

6

ZS

Transport and base plates GN 80i affix attachments such as leveling feet or castors to aluminum profiles.

They are installed in the profile holes on the end faces using suitably tapped threaded holes or thread-forming screws. Transport and base plates can also be fastened lengthwise in the profile slot.

see also ...

- Aluminum Profiles GN 10i (Profile Type Light) → Page QVX
- Aluminum Profiles GN 10i (Profile Type Heavy) → Page QVX
- Aluminum Profiles GN 11i (with Partially Closed Slots) → Page QVX

How to order 1 S₁ 2 S₂ 3 n 4 d_1 ٤ð J. 6 2 5 Type GN 80i-40808M10-A-ZS 6 Material / Color

3.7 Connecting, Assembling with Clamping and Connecting Elements

Page 1



Assembly Instructions / Profile Machining

