




d ₁ h11	d ₂	d ₃ Round workpiece	d ₄ H7	d ₅	e +0,2	l ₁ max.	l ₂	l ₃	A/F	Max. tightening torque in Nm	Code No. Mounting tool
8	M 4	6 ... 10	8	M 2,5	d ₃ / 2 + 2,8	27	8	4	3	2,9	GN 928.1-3
10	M 5	10 ... 15	10	M 3	d ₃ / 2 + 3,3	33	10	5	4	6	GN 928.1-4
12	M 6	15 ... 20	12	M 4	d ₃ / 2 + 3,5	39	12	6	5	10	GN 928.1-5
16	M 8	20 ... 30	16	M 5	d ₃ / 2 + 4	46	16	8	6	25	GN 928.1-6
20	M 10	30 ... 40	20	M 6	d ₃ / 2 + 4,8	53	20	10	8	46	GN 928.1-8
25	M 12	40 ... 60	25	M 8	d ₃ / 2 + 5,6	70	25	12	10	82	GN 928.1-10
30	M 16	60 ... 125	30	M 10	d ₃ / 2 + 7,9	81	30	16	14	206	GN 928.1-14

Specification	
Clamping element	
• Steel	—
• Blackened	
• Stainless steel AISI 303	NI
Socket cap screw ISO 4762	
• Steel, zinc plated, blue passivated	
• Stainless steel for NI	

RoHS	
Technical Information	Page
ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX
Accessory	
GN 928.1 Mounting Tools (Code no. see table)	QVX

How to order (Steel)

1

GN 928-16

1

d₁

How to order (Stainless steel)

1

GN 928-8-NI

2

Material