



1.1

1.2

1.3

1.4



b	d ₁	d ₂	l ₁	l ₂	l ₃	l ₄	m ₁	m ₂
24	B 6 B 8 B 10	3,2	38	28	8	29,5	15	18

2.1

Specification

- Plastic
Technopolymer (Polyamide PA-HP)
- Temperature resistant up to 80 °C
- Black, matte finish
- Adjustable hand lever
- Plastic
Technopolymer (Polyamide PA)
Glass fiber reinforced
Black, matte finish
- Threaded bushing
Stainless steel AISI 304
- Hex head screw
Stainless steel AISI 316
- *Stainless Steel Characteristics* → Page QVX
- RoHS

Information

Clamping plates GN 955.6 are used in connection with position indicators GN 955 / GN 955.2. The mounting holes support typical bore hole patterns.

In a simpler manner and without great construction and installation effort these spindles can, after adjustment, be clamped and locked.

At the same time these plates are fitted with bore diameter 6.1 to accommodate the torque support of the position indicator.

The clamping plate can be installed so that the hand lever is situated as required either on the right or the left.

see also...

- *Position Indicators GN 955 (Hollow Shaft Steel)* → Page QVX
- *Position Indicators GN 955.2 (Hollow Shaft Stainless Steel)* → Page QVX

2.2

2.3

2.4

How to order

GN955.6-24-B6

1	b
2	d ₁

