




d ₁ Plunger h9 +0,08 Bore +0,03	l ₁	d ₂		d ₃	l ₂	l ₃	l ₄	l ₅ ≈	l ₆ ≈	l ₇ ≈	A/F
		Coding R	Coding F								
4	5	M 10	M 10 x 1	17	8	20	26	2	30	47	15
5	5	M 10	M 10 x 1	17	8	20	26	2	30	47	15
6	7	M 12	M 12 x 1,5	22	10	27	35	3	40	63	19
7	7	M 12	M 12 x 1,5	22	10	27	35	3	40	63	19
8	10	M 16	M 16 x 1,5	26	12	33	43	3	51	78	22
10	10	M 16	M 16 x 1,5	26	12	33	43	3	51	78	22

Specification	
Guide	
• Steel	ST
• Zinc plated, blue passivated	
• Stainless steel AISI 303	NI
Plunger pin	
Stainless steel AISI 303	
Lever	
Plastic, polyptalamide (PPA)	
• Glass fiber reinforced	
• Black	● SW
Pressure spring	
Stainless steel AISI 302	
RoHS	
Technical Information	Page
Overview of Indexing Plungers	QVX
Load Rating Information	QVX
Metric ISO Fine Thread DIN 13	QVX
ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX

Indexing plungers GN 823 with operating lever can be used to lock carriages in guides, for example. The plunger pin is retracted by simply pressing the operating lever.

Type C also allows actuation by pulling and locking the plunger pin in the retracted position (rest position).

see also...		Page
GN 823 Indexing Plungers		
(with Operating Lever, with Flange for Surface Mounting)		QVX
GN 822.6 Mini Indexing Plungers (Steel, with Knob)		QVX
GN 822.7 Mini Indexing Plungers (Stainless Steel, with Knob)		QVX
Accessory		
GN 412.2 GN 412.4 Positioning Bushings (with Collar)		QVX
GN 412.3 GN 412.5 Positioning Bushings (with Ramping Cone)		QVX
GN 609.5 Distance Bushings (Stainless Steel)		QVX
GN 412.1 Mounting Blocks (Zinc Die Casting)		QVX
GN 612.1 Mounting Blocks (Steel)		QVX
GN 909 GN 909.5 Thin Hex Nuts		QVX

How to order		1	d ₁
		2	l ₁
		3	Type
		4	Coding
		5	Material
		6	Color
GN823-10-10-B-R-NI-SW			