



- 3 Type
- D With plain shaft
 - E With threaded shaft

d ₁	d ₂ h8 Type D		d ₃ Type E		d ₄ h13	l ₁ ≈	l ₂	l ₃	A/F Internal hexagon
	ST / AL	KT	ST / AL	KT					
16	7	7	M 6	M 6	10	49	11	5,5	3
20	8	8	M 8	M 8	13	61	13	6	4
25	10	10	M 10	M 10	16	75	14	8	5
32	13	13	M 12	M 12	20	95	21	10,5	6
36	16	-	M 16	-	22	106	26	11	8

Specification

- Steel **ST**
Zinc plated, blue passivated
- Aluminum **AL**
Glossy finish
- Plastic **KT**
Technopolymer (Polyamide PA)
- Temperature resistant up to 110 °C
- Black, matte finish
- Spindle
Steel
Zinc plated, blue passivated
- ISO Fundamental Tolerances → Page 2151
- Plastic Characteristics → Page 2158
- RoHS

Information

Revolving handles DIN 98 type D are supplied unassembled so that the shaft can be press fitted or screwed into a tapped blind bore prior to assembly.

Light taps with a soft-head hammer in the axial direction affix the handle to the axle with sufficient firmness that it is held in place axially while still remaining turnable.

How to order		1	Material
DIN 98-KT-32-D		2	d ₁
		3	Type