



d Ø	w	l ₁	l ₂	For tube
D 10	1 ... 2	3,5	11	GN 990
D 12	1 ... 2	3,5	11	GN 990
D 13	1 ... 2	4	11	¼"
D 14	1 ... 2	5	11,5	GN 990
D 15	1 ... 2	3	11,5	GN 990
D 16	1 ... 2	5	11	GN 990
D 18	1 ... 2	5	11,5	GN 990
D 20	1 ... 2,5	5	11,5	GN 990
D 22	1 ... 2	5	11,5	-
D 25	1 ... 3	5	11,5	GN 990
D 26	1 ... 3	5	11,5	-
D 27	1 ... 3	5	11,5	¾"
D 28	1 ... 3	5	11,5	-
D 30	1 ... 2,5	5	11,5	GN 990
D 32	1 ... 3	5	12	GN 990
D 34	1 ... 3	5	11,5	1"

d Ø	w	l ₁	l ₂	For tube
D 35	1 ... 3	5	11,5	GN 990
D 36	1 ... 3	5	11,5	-
D 38	1 ... 3,5	5	11,5	-
D 40	1 ... 3	5	11,5	GN 990
D 42	1 ... 3	5	11,5	GN 990
D 45	1 ... 3	5	11	GN 990
D 48	1,2 ... 3,6	5	11,5	GN 990
D 50	2,5 ... 4,5	5	11,5	GN 990
D 55	3 ... 5	5	14,5	GN 990
D 60	3 ... 5	5	17,5	GN 990
D 70	1,5 ... 3,5	5	21	-
D 76	1,6 ... 4	6	21,5	2 ½"
D 80	1,5 ... 3	5	22	-
D 88	1,5 ... 4	6	21,5	3"
D 90	1,5 ... 5	6	21	-
D 100	2 ... 4,5	6	28,5	-

s ∅	w	l ₁	l ₂	For tube
V 10	0,8 ... 2,5	4	12	GN 990
V 12	1 ... 2	4	12	GN 990
V 15	1 ... 2	3	11,5	-
V 16	1 ... 2,5	5	11,5	GN 990
V 18	1,5 ... 3	5	11,5	-
V 20	1 ... 3	5	11,5	GN 990
V 22	1 ... 3,5	5	12	-
V 25	1 ... 3	5	11,5	GN 990
V 30	1 ... 3	5	11,5	GN 990
V 34	1 ... 3	5	14,5	-
V 35	1 ... 3	5	11,5	GN 990
V 40	1 ... 3	5	14,5	GN 990
V 45	1 ... 3	5	14,5	GN 990
V 50	2,6 ... 4	5,5	24	GN 990
V 55	2 ... 4,5	5	14,5	-
V 60	1,5 ... 3,5	5	15	-
V 70	2 ... 5	5	22	-
V 80	1,5 ... 4	6	21	-
V 90	3 ... 5	6	21	-
V 100	1 ... 4	7	21	-

Specification

- Plastic Technopolymer (Polyethylen PE)
 - Black, RAL 9005, matte finish **SW**
 - Gray, RAL 7042, matte finish **GR**
- *Plastic Characteristics* → Page 2158
- **RoHS**

On request

- Other sizes
- White, RAL 9003, matte finish **WS**



Information

Tube end plugs GN 991 have been designed for sealing tube ends for safety or optical reasons.

They are pressed into the tube end either by hand or with a mallet.

see also...

- *Construction Tubes GN 990* → Page 1835
- *Retaining Rods / Retaining Tubes GN 480.1* → Page 1833
- *Insert Bushings GN 992 (Aluminum, with Internal Thread)* → Page 1501

How to order

GN 991-V25-GR

1 s (d)

2 Color