


**Application example**



1		1		2		l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub> +0,5	w	For tube GN 990	
d <sub>1</sub>		s		d <sub>2</sub>							
GN 992 Outside-Ø for round tube	GN 992.5 Outside-Ø for round tube	GN 992 Outside- $\square$ for square tube	GN 992.5 Outside- $\square$ for square tube			GN 992	GN 992.5				
D 20	D 20	V 20	V 20	M 8	-	29,5	29,5	2,5	16	2	D20 / V20
D 25	D 25	V 25	V 25	M 8	M 10	33,5	29,5	2,5	16	2	D25 / V25
D 30	D 30	V 30	V 30	M 8	M 10	33,5	29,5	2,5	18	2	D30 / V30
D 32	-	-	-	M 8	M 10	33,5	-	2,5	18	2	D32
D 35	-	V 35	-	M 10	M 12	37,5	-	2,5	24	2	D35 / V35
D 40	D 40	V 40	V 40	M 10	M 12	41,5	33,5	2,5	24	3	D40 / V40
D 42	-	-	-	M 10	M 12	41,5	-	2,5	24	3	D42
D 45	-	V 45	-	M 12	M 16	45,5	-	2,5	30	3	D45 / V45
D 48	-	-	-	M 12	M 16	45,5	-	2,5	30	3	D48
D 50	D 50	V 50	V 50	M 12	M 16	45,5	37,5	2,5	30	3	D50 / V50

**Specification**

- **GN 992**  
Aluminum  
Plain
- **GN 992.5**  
Stainless steel AISI 303
- *Stainless Steel Characteristics* → Page 2166
- RoHS

**Information**

Drive the insert bushings GN 992 / GN 992.5 in by using a soft-head mallet. Their lamellas bridge a production tolerance of the internal diameter or of the internal square of  $\pm 0.5$  mm, allowing screws to be mounted in tubes.

The dimensions match those of the construction tubes GN 990, but checking the tolerance position of the tube is recommended.

see also...

- *Construction Tubes GN 990* → Page 1835

**How to order (Aluminum)**

1 d<sub>1</sub> (s)  
2 d<sub>2</sub>

**GN 992-D40-M10**

**How to order (Stainless steel)**

1 s (d<sub>1</sub>)  
2 d<sub>2</sub>

**GN 992.5-V25-M8**