



3.1

3.2

3.3

d <sub>1</sub>	d <sub>2</sub>	1							2			I <sub>2</sub>	A/F	Static load in kN (see information)
		GN 839							GN 839.5					
25	M 6	26	36	56	64	-	-	-	26	36	56	11	13	1,5
25	M 8	19	24	34	54	74	-	-	24	34	54	11	13	2,5
30	M 6	24	34	54	-	-	-	-	24	34	54	12	17	1,5
30	M 8	18	23	33	53	73	-	-	23	33	53	12	17	2,5
30	M 10	18	23	33	43	53	63	73	33	53	73	12	17	3
40	M 8	14	22	32	52	72	-	-	22	32	52	13,5	17	2,5
40	M 10	22	32	42	52	62	72	102	32	52	72	13,5	17	3
40	M 12	52	72	102	-	-	-	-	52	72	102	13,5	17	5
50	M 10	48	68	98	-	-	-	-	48	68	98	17	19	3
50	M 12	48	68	98	-	-	-	-	48	68	98	17	19	5
60	M 12	46	66	96	-	-	-	-	46	66	96	19	24	5
60	M 16	66	106	146	-	-	-	-	66	106	146	19	24	7,5

3.4

3.5

3.6

**Specification**

- Foot  
Technopolymer (Polyamide PA)  
- Black, matte finish  
- Temperature resistant up to 100 °C
- **GN 839**  
Screw  
Steel  
Zinc plated, blue passivated
- **GN 839.5**  
Screw  
Stainless steel AISI 304
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

**Information**

Leveling feet GN 839 / GN 839.5 are used for applications in cases where no jointed link is required between foot and adjusting screw. The cross slot drive at the underside has been designed for rapid pre-assembly.

The value for the load-bearing capacity given in the table is an approximate value which, depending on conditions of use, may cause the plastic leveling feet to break. The appropriate safety coefficient must be taken into account.

see also...

- *Ball Jointed Leveling Feet GN 638* → Page 1444

3.7

3.8

3.9

How to order (Screw steel)	1	d <sub>1</sub>
	2	d <sub>2</sub>
	3	l <sub>1</sub>
<b>GN 839-25-M8-34</b>		

How to order (Screw stainless steel)	1	d <sub>1</sub>
	2	d <sub>2</sub>
	3	l <sub>1</sub>
<b>GN 839.5-30-M8-53</b>		