



3 Type
M Straight lever
N Angled lever

1 d ₁	2 d ₂		d ₃	d ₄	h ₁	h ₂	h ₃ ≈	l ₂	l ₃ ≈	t min.
10	M 6	M 8	13,5	20	25	8	39,5	63	60	12
13	M 8	M 10	16	25	29	8	49,5	80	76	15
16	M 10	M 12	19	28	33,5	10,5	60,5	100	95	18

Specification

- Steel
Blackened
- RoHS

Information

Adjustable clamping levers GN 99.2 are known for their small dimensions. They are for use in applications where either the clamping range is limited or where a specific lever position is required. The serrated bore in the spherical hub is fitted with a threaded bolt insert which engages in the hub with its own serrations.

By depressing the clamping lever the serrations are disengaged freeing it for re-positioning in the most convenient position. When releasing the lever the serrations will re-engage automatically.

Should a rotation of 360° not be possible the insert can be slightly screwed in (after the lever has been disengaged) by means of the slotted knurled screw.

see also...

- Clamping Levers DIN 99 (Steel / Stainless Steel) → Page 502

How to order

GN 99.2-16-M12-N

- 1** d₁
- 2** d₂
- 3** Type