



1

Size	F_H in N Holding capacity	a_1	a_2	b_1	b_2	b_3	b_4	b_5	b_6	b_7	d_1	d_2	d_3
1400	12000	15	29	61	61	46	26	64	42	26	M 10	8,5	32,5

Size	$h_1 \approx$	h_2	$l_1 \approx$	l_2 min.	m_1	m_2	m_3	m_4	m_5	$r \approx$ at $w_2 = 0$	s	w_1 Stroke	$w_2 \approx$ Adjustable range
1400	64	24	171	42	38	14,5	32	12,5	17	109	8	50	22

- Specification
- Body / Clamping lever
Steel C22
 - Forged
 - Blackened
 - Catch
Sheet steel
Blackened
 - Square U-bolt / Bearing pins
Steel St 37
Zinc plated, blue passivated
 - All moving parts
Lubricated with special grease
 - RoHS

Information

The square U-bolt of latch type toggle clamps GN 852.1 is adjustable within the adjusting range.

In the clamped position the square U-bolt is perpendicular to the clamping arm and the fixing plane of the latch type toggle clamp.

In addition to the standard lengths of the square U-bolt shown in the table, a variety of other lengths are also available under the GN 951.2 series.

see also...

- General Information for Toggle Clamps → Page 698
- Square U-Bolts GN 951.2 → Page 775

