

- 2 Type**
- T5** Without latch bolt, without catch
 - TG** With oval head latch bolt, with catch
 - TT** With T-head latch bolt, with catch
 - TU** With J-hook latch bolt, with catch

1

Size	F _H in N Holding capacity	a	b ₁	b ₂	b ₃	b ₄	b ₅	b ₆	b ₇	d ₁	d ₂	d ₃	d ₄	d ₅	h ₁ ≈
160	1750	13	26	28	23	14	26	35	6,8	M 6	4,5	4,5	5,2	6	27
320	4000	19	40	44	34	18	35	38	10	M 8	6,7	6,7	7	8	38,5
700	7500	28	60	54	41	26	50	50	11	M 10	8,5	8,5	9	10	53

Size	h ₂	h ₃	l ₁ ≈	l ₂ ≈ Type TG	l ₃ ≈ Type TT	l ₄ ≈ Type TU	l ₅	l ₆	m ₁	m ₂	m ₃	m ₄	m ₅	s	w Stroke
160	20	20,5	103	55	55	54	28	30	19	16	16	14,3	25,4	2	8
320	30	28	153	76,5	76,5	76,5	34	44,5	32	19	19	22,3	25,4	3	13
700	40,5	39	222	95,5	93	92	42	51	38	41,5	31	25,4	31	3,5	19

Specification

- Sheet metal parts
Case-hardened Steel C10
Blackened
- Latch bolt
Steel St 32
Blackened
- All moving parts
Lubricated with special grease
- Handle with plastic cap
Red, oil resistant
- RoHS

Information



Latch type toggle clamps GN 853 feature a locking mechanism which prevents an inadvertent or vibration-induced opening of the clamp. Another benefit is the option of operating the clamp with one hand.

see also...



- *Stainless Steel Latch Type Toggle Clamps GN 853* → Page 778

<p>How to order</p> <p>GN 853-320-TT</p>	1	Size
	2	Type



Type **TG**
Oval head latch bolt




Type **TT**
T-head latch bolt




Type **TU**
J-hook latch bolt




Description of function (for one-hand operation)




Press the release button for **releasing**.




Lift the clamping arm until the latch bolt disengages from the catch.



Retracting the clamping arm will lift the latch bolt and release the catch (one-hand operation).



For **clamping operation**, lift the clamping arm until it rests on the catch.



The clamping arm engages in the catch if the release button is pressed for the clamping operation.

When clamping in the end position, the system locks automatically by spring force.

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4