








Standard	Shaft Ø in mm	Hub clamping	Rated torque in Nm	Misalignment			Zero backlash	
				Axial	Lateral	Angular		
<b>GN 2240</b> <a href="#">Page XYZ</a> <b>Elastomer jaw couplings</b>		3 ... 25		0,7 ... 60	x	x	x	-
<b>GN 2241</b> <a href="#">Page XYZ</a> <b>Elastomer jaw couplings</b>		3 ... 25		0,7 ... 60	x	x	x	-
<b>GN 2242</b> <a href="#">Page XYZ</a> <b>Oldham couplings</b>		4 ... 20		1 ... 28	-	x	x	-
<b>GN 2243</b> <a href="#">Page XYZ</a> <b>Oldham couplings</b>		2 ... 20		0,5 ... 28	-	x	x	-
<b>GN 2244</b> <a href="#">Page XYZ</a> <b>Bellows couplings</b>		5 ... 19		1,5 ... 10	x	x	x	x
<b>GN 2246</b> <a href="#">Page XYZ</a> <b>Beam couplings</b>		4 ... 12		0,3 ... 4	x	x	x	x
<b>GN 2250</b> <a href="#">Page XYZ</a> <b>Double loop couplings</b>		6 ... 10		0,5 ... 2	x	x	x	-

Standard	Suitable for use with			Application examples	Special features
	Servo motors	Stepper motors	Universal motors		
<b>GN 2240</b> Page XYZ <b>Elastomer jaw couplings</b>	x	x	x	<ul style="list-style-type: none"> <li>- Hydraulic pumps</li> <li>- Packaging machines</li> <li>- Industrial robots</li> <li>- Fans</li> <li>- Agitators</li> </ul>	<ul style="list-style-type: none"> <li>- High torques</li> <li>- Fast and simple plug-in assembly</li> </ul>
<b>GN 2241</b> Page XYZ <b>Elastomer jaw couplings</b>	x	x	x		
<b>GN 2242</b> Page XYZ <b>Oldham couplings</b>	-	x	x	<ul style="list-style-type: none"> <li>- Conveyor systems</li> <li>- Packaging machines</li> <li>- Positioning drives</li> <li>- Pumps</li> </ul>	<ul style="list-style-type: none"> <li>- High torques</li> <li>- High lateral misalignment compensation</li> <li>- Fast and simple plug-in assembly</li> </ul>
<b>GN 2243</b> Page XYZ <b>Oldham couplings</b>	-	x	x		
<b>GN 2244</b> Page XYZ <b>Bellows couplings</b>	x	x	-	<ul style="list-style-type: none"> <li>- Rotary encoders</li> <li>- Position measuring systems</li> <li>- Test benches</li> <li>- Industrial robots</li> <li>- Spindle drives</li> </ul>	<ul style="list-style-type: none"> <li>- Precise angle and torque transmission</li> <li>- High torsional stiffness</li> </ul>
<b>GN 2246</b> Page XYZ <b>Beam couplings</b>	-	x	-	<ul style="list-style-type: none"> <li>- Confectionery machines</li> <li>- Industrial robots</li> <li>- CAT scanners</li> <li>- Position measuring systems</li> </ul>	<ul style="list-style-type: none"> <li>- Precise angle and torque transmission</li> <li>- Manufactured from a single piece</li> <li>- High torsional stiffness</li> </ul>
<b>GN 2250</b> Page XYZ <b>Double loop couplings</b>	-	x	-	<ul style="list-style-type: none"> <li>- Plant engineering</li> <li>- Elevator technology</li> <li>- Measurement technology</li> <li>- Chemical industry</li> <li>- Food industry</li> </ul>	<ul style="list-style-type: none"> <li>- High misalignment compensation</li> <li>- FDA compliant material</li> </ul>

3.1

3.2

3.3

3.4

3.5

3.6

3.7

3.8

3.9

