



- 2 Type**
- APVS** Forked clamping arm, with two flanged washers
- CPVS** Forked clamping arm, with two flanged washers and clamping screw GN 708.1
- EPVS** Solid clamping arm, with clasp for welding
- 3 Coding**
- M** Magnetic piston



Size	F _H in N Holding capacity	F _S in N Clamping force at 6 bar ≈	a	b ₁	b ₂	b ₃	b ₄	b ₅	d ₁	d ₂	d ₃ Com-pressed air connections	Inside Ø Connection tube	e	h ₁	h ₂	h ₃	h ₄ ≈
230	2200	1260	40	58	38	46	51	8,5	M 8	6,5	G 1/8	4	41,5	302	87	18	30
330	2600	1800	45	70	52,5	56	79	10,5	M 10	8,5	G 1/4	6	52,5	363	108	22	37

Size	h ₅	l ₁ ≈ Type APVS Type CPVS	Type EPVS	l ₂ ≈	l ₃ ≈ max.	l ₄	m ₁	m ₂	m ₃	m ₄	m ₅	m ₆	r ≈ Type APVS Type CPVS	Type EPVS	s ₁	s ₂	s ₃	w Adjustable range
230	63	153	155	67	81	68	26	14	16	11	16	14,2	104	105	3	5,5	6	20
330	80	182	184	72	91	77	30	16	28	19	30	20	121	123	3,5	6,5	7	19

