



For swing clamps Size	² d ₁	³ m	b	d ₂	d ₃	h ₁	h ₂	Length l
16	8	41	12,5	M 4	5,5	9	5,5	53,5
20	12	48	17	M 5	8,5	10	5,5	65
25	14	50	18	M 6	8,5	10	6,5	68
32	16	60	20	M 8	8,5	12	9	80
40	16	70	20	M 8	8,5	15	9	90
50	20	80	25	M 10	10,5	16	10	105
63	20	90	25	M 10	10,5	18	10	115

Specification

- Aluminum **AL**
- Hard anodized **HE**
- Wear-resistant surface
- Socket cap screw DIN 912
Steel, zinc plated, blue passivated
- Washer ISO 7092
Steel, zinc plated, blue passivated
- RoHS

Accessory

- Clamping Screws GN 708.1 → Page 812

Information

Clamping arms GN 875.3 with threaded hole designed as accessories to swing clamps GN 875 / GN 876. The thread can receive an application-specific clamping bolt.

The angle orientation of the clamping arm can be set arbitrarily during mounting on the swing clamp. When tightening the screw, the piston rod must not experience any torque. The clamping arm must therefore be held to prevent twisting.

Included are a socket cap screw DIN 912 and a washer ISO 7092 for fastening to the swing clamp.

see also...

- *Swing Clamps GN 875 (in Block Version)* → Page 842
- *Swing Clamps GN 876 (with Screw-In Thread)* → Page 844

How to order

GN 875.3-AL-16-60-HE

- 1 Material
- 2 d₁
- 3 m
- 4 Finish

