


3 Type

- A** Without retaining bores
- B** With retaining bores for rotary tables

Mounting example



1

2

b Size of the slide	l₁	d₁ Socket cap screws DIN 912	d₂ For socket cap screws DIN 912 Type B	h₁	h₂	l₂	Type B for rotary tables
30	41	M 2,5	-	5	4,2	35,4	-
50	67	M 3	5,5	8	7	58	GN 900.6-55
80	105	M 4	5,5	12	12,5	92	GN 900.6-80
120	145	M 5	5,5	16	13,8	131,8	GN 900.6-80

Specification

- Aluminum
Anodized, natural color
- Socket cap screws DIN 912
Stainless steel
- RoHS

Information

Mounting plates GN 900.4 type A are used for installing fixtures on the operator's side. Type B is used for installing a rotary table GN 900.6.

The mounting plate can be simply clamped on to the slide and no additional drilled holes are required.

The small fixing plates serve as an additional fine adjustment of the mounting plate with the adjustable slide unit.

All parts required to make up a set are included.

see also...

- *Adjustable Slide Units GN 900* → Page 1938
- *Rotary Tables GN 900.6* → Page 1946

How to order

GN 900.4-50-67-B

- 1** b
- 2** l₁
- 3** Type