



1 2

b	d <sub>1</sub> F9					d <sub>2</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	l <sub>5</sub>	m <sub>1</sub>	m <sub>2</sub>	m <sub>3</sub>	m <sub>4</sub>	m <sub>5</sub>
48	B 12	B 14	B 15	B 16	B 20	5,5	73	40,5	18	24,5	30	34	36	33,6	25	17

**Specification**

- Zinc die casting  
Powder coated  
Black, textured finish
- Adjustable hand lever GN 302.1  
- Zinc die casting  
Powder coated  
Black, RAL 9005, textured finish  
- Threaded insert  
Stainless steel AISI 303 → Page 451
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166
- RoHS

**Information**

Clamping plates GN 9053.6 are used in connection with position indicators GN 9053 / GN 9153. The mounting holes support typical hole patterns.

In a simpler way and without large construction and installation effort these spindles can, after adjustment, be clamped and locked.

At the same time these plates are fitted with the bore Ø 6,1 to accept the torque limiting contact point for the position indicator.

The clamping plate can be installed so that the hand lever is positioned either to the right or the left.

see also...

- Position Indicators GN 9053 → Page 402
- Position Indicators GN 9153 → Page 406

How to order

**GN9053.6-48-B12**

- 1 b
- 2 d<sub>1</sub>

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

