



3 Type

- A** Without sealing ring
- AC** With sealing ring in copper
- AA** With sealing ring in aluminum
- AN** With sealing ring in stainless steel

2

d ₁			d ₂ h14	d ₃	d ₄	l ₁ ±0,2	l ₂ +0,5	s	A/F
Steel ST	Stainless steel A4	Steel ST Stainless steel A4			Sealing Outside diameter				
M 8 x 1	M 8 x 1	-	12	8,3	11,5	8	3	1	4
M 10 x 1	M 10 x 1	-	14	10,3	13,5	8	3	1	5
-	-	G 1/8	14	10	13,5	8	3	1	5
M 12 x 1,5	M 12 x 1,5	-	17	12,3	16	12	3	1,5	6
-	-	G 1/4	18	13,4	18	12	3	1,5	6
M 14 x 1,5	M 14 x 1,5	-	19	14,3	18	12	3	1,5	6
M 16 x 1,5	M 16 x 1,5	-	21	16,3	20	12	3	1,5	8
-	-	G 3/8	22	17	21	12	3	1,5	8
M 18 x 1,5	M 18 x 1,5	-	23	18,3	22	12	4	1,5	8
M 20 x 1,5	M 20 x 1,5	-	25	20,3	24	14	4	1,5	10
-	-	G 1/2	26	21,3	26	14	4	1,5	10
M 22 x 1,5	M 22 x 1,5	-	27	22,3	27	14	4	1,5	10
M 24 x 1,5	M 24 x 1,5	-	29	24,3	29	14	4	2	12
M 26 x 1,5	-	-	31	26,3	31	16	4	2	12
M 27 x 2	-	-	32	27,3	32	16	4	2	12
-	-	G 3/4	32	26,7	32	16	4	2	12
M 30 x 1,5	-	-	36	30,3	36	16	4	2	17
M 33 x 2	-	-	39	33,3	39	16	5	2	17
-	-	G 1	39	33,5	39	16	5	2	17
M 42 x 2	-	-	49	42,3	49	16	5	2	22
-	-	G 1 1/4	49	42,2	49	16	5	2	22
M 48 x 2	-	-	55	48,3	55	16	5	2	24
-	-	G 1 1/2	55	48,1	55	16	5	2	24

Specification

Threaded plug

- Steel **ST**
 - Zinc plated, blue passivated
 - Property class 5.8
- Stainless steel AISI 316 / AISI 316Ti **A4**

Sealing ring DIN 7603

for type AC / AA / AN

RoHS

Technical Information

	Page
ISO Fundamental Tolerances	QVX
Strength Values of Screws	QVX
Stainless Steel Characteristics	QVX

Threaded plugs DIN 908 are used, for example, on filling, drain or inspection openings of gear boxes and hydraulic tanks.

see also...

	Page
GN 746 Threaded Plugs (Plastic)	QVX
GN 749 Threaded Plugs (with rubber sealing)	QVX
DIN 910 Threaded Plugs (with external hex)	QVX

Accessory

DIN 7603 Sealing Rings	QVX
-------------------------------	-----

How to order		1	Material
1	2	3	d ₁
DIN 908-ST-M24x1,5-AN			3
			Type