



d₁	d₂ H9	b₁^{-0,05 -0,15}	b₂	d₃	d₄ Gear lever handle	Length l	r₁	r₂	r₃	r₄	s	t min.
24	B 8	13	11	M 6	8	28	12	13,32	14,64	15,3	3,3	9
30	B 10	15	13	M 8	10	32	15	16,65	18,3	19,12	4,1	12
35	B 12	17	15	M 10	12	36	17,5	19,42	21,34	22,31	4,8	15

Specification

- Sintered Steel
 - Case-hardened
EHT 0,2 to 0,4 mm
 - Plain
- *ISO Fundamental Tolerances* → Page 2151
- RoHS

Accessory

- Gear Lever Handles GN 310 → Page 90
(to be ordered separately)

Information

Hubs with eccentric cam GN 919 are used for adjusting and clamping operations. As a rule these are fitted with a gear lever handle GN 310.

The cam offers the advantage that the clamping force remains constant in every position of its travel. In addition the cam is self locking.

Cylinder head shoulder bolts GN 732.1 can be used as bearing pins.

see also...

- *Cylinder Head Shoulder Bolts GN 732.1* → Page 1057
- *Eccentric Cams GN 918* → Page 668

How to order

GN 919-35-B12

1 d₁

2 d₂