


Disk handwheel

Spoked handwheel



**3 Type**

- A** Without handle
- R** With revolving handle
- RU** With revolving retractable handle



1

2

d <sub>1</sub> Ø Linear actuator	d <sub>2</sub> Disk handwheel	Spoked handwheel	d <sub>3</sub> H7 Bore	l <sub>1</sub> ≈	l <sub>2</sub> ≈	l <sub>3</sub> ≈	l <sub>4</sub> ≈	Ø Handle GN 599.5	Ø Handle GN 798.2	Ø Handle GN 798.3
18*	50	-	6	26	20	-	-	13	-	-
18*	80	-	6	26	43,5	-	-	-	16	-
25*	63	-	8	27	20	-	-	13	-	-
25	100	-	8	30	58	39	56,5	-	18	18
30*	63	-	8	27	20	-	-	13	-	-
30	100	-	8	30	58	39	56,5	-	18	18
40	100	-	12	30	58	39	56,5	-	18	18
40	-	125	12	33,5	61,5	45	60,5	-	22	22
50	-	140	12	36,5	76,5	47	75,5	-	24	24
60	-	160	14	39,5	76,5	48	75,5	-	24	24

**Specification**

- Aluminum die casting
  - Machined hub
  - Turned rim
  - Powder coated  
Black, RAL 9005, textured finish ● **SW**
- Concentricity and axial run-out tolerance of the rim < 0.4
- Revolving handles / Retractable handles / Revolving cylinder handles  
GN 798.2 / GN 798.3 / GN 599.5
- Keyway JS9 DIN 6885 Page 1 → Page 2078
- Cross Holes GN 110 → Page 2080
- ISO Fundamental Tolerances → Page 2151
- RoHS

4

**Information**

\* only available in type A and R

Handwheels GN 9234 are intended for use with linear actuators and are designed as disk or spoked handwheels, depending on their size.

The applied torque is transmitted by means of a parallel key, and the handwheel is secured axially with the supplied grub screw. The handwheels can be ordered without handles, with revolving handles or with revolving retractable handles.

**How to order**

**GN9234-30-100-R-SW**

- 1 d<sub>1</sub>
- 2 d<sub>2</sub>
- 3 Type
- 4 Finish