



## 2 Bore code

- B** Without keyway  
**K** With keyway DIN 6885-1 P9

## 4 Type

- A** Without handle  
**F** With fixed handle

<b>1</b> $d_1$	<b>3</b> $d_2$ H9 Bore	$b$	$d_3 \approx$	$d_4$	$l_1$	$l_2 \approx$	$l_3$	$r$	$\emptyset$ Handle	No. of spokes
100	10	14,5	25,5	M 6	17	33	48,5	36	16	3
125	12	15,8	27	M 8	18	35,5	62	47	20	3
140	14	17	29	M 8	19	38,5	62	52	20	3
160	14	17,5	31	M 10	20	39,5	77	62	25	3
200	18	20	37	M 10	24	44,5	77	80	25	3

## Specification

### Wheel body

Stainless steel precision casting AISI 316

- Acid resistant (A4 quality)
- Hub machined
- Rim turned and polished
- Unmachined surface matte shot-blasted

### Fixed handle DIN 39

Stainless steel AISI 316L

Acid resistant (A4 quality)

RoHS

## On request

- Other bore- $\emptyset$
- With square

The dimensions of the handwheels GN 950.6 comply extensively with handwheels DIN 950.

## see also...

**DIN 950** Handwheels (Cast Iron, Aluminium) Page QVX

## Technical Information

Keyways P9 DIN 6885-1 QVX

Cross holes GN 110 QVX

ISO Fundamental Tolerances QVX

Stainless Steel Characteristics QVX

## Accessory

**GN 184.5** Countersunk Washers (for Axial Fastening) QVX

## How to order

**GN 950.6-160-B14-F**

<b>1</b>	$d_1$
<b>2</b>	Bore code
<b>3</b>	$d_2$
<b>4</b>	Type