



<sup>1</sup> d <sub>1</sub> f7	<sup>2</sup> d <sub>2</sub> H7 Bore							<sup>3</sup> l <sub>1</sub>	d <sub>3</sub>	l <sub>2</sub>	For position indicators
10	B 6	B 8	-	-	-	-	-	20	3,2	2,5	GN 955
14	B 6	B 8	B 10	B 12	-	-	-	20	4,25	3,5	GN 954 / GN 9054
20	B 6	B 8	B 10	B 12	B 14	B 15	B 16	20	5,5	4,5	GN 953 / GN 9053 / GN 9153

**Specification**

- Steel Blackened —
- Stainless steel AISI 304 **NI**
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166
- RoHS



**Information**

With the help of adapter bushings GN 952.1 position indicators can be adapted to accept different smaller spindle diameters.

The adapter bushings are supplied with a set screw.

see also...

- Position Indicators GN 953 → Page 396
- Position Indicators GN 954 → Page 398
- Position Indicators GN 955 → Page 400
- Position Indicators GN 9053 → Page 402
- Position Indicators GN 9054 → Page 404
- Position Indicators GN 9153 → Page 406

How to order (Steel)		1	d <sub>1</sub>
<b>GN 952.1 -14-B12-20</b>		2	d <sub>2</sub>
<sup>1</sup>	<sup>2</sup>	3	l <sub>1</sub>

How to order (Stainless steel)		1	d <sub>1</sub>
<b>GN 952.1-10-B8-20-NI</b>		2	d <sub>2</sub>
<sup>1</sup>	<sup>2</sup>	3	l <sub>1</sub>
<sup>3</sup>	<sup>4</sup>	4	Material