



1 2

<b>b</b>	<b>d<sub>1</sub> F9</b>					<b>d<sub>2</sub></b>	<b>l<sub>1</sub></b>	<b>l<sub>2</sub></b>	<b>l<sub>3</sub></b>	<b>l<sub>4</sub></b>	<b>l<sub>5</sub></b>	<b>m<sub>1</sub></b>	<b>m<sub>2</sub></b>	<b>m<sub>3</sub></b>	<b>m<sub>4</sub></b>	<b>m<sub>5</sub></b>
48	B 12	B 14	B 15	B 16	B 20	5,5	66,5	43	15	24,5	30	34	36	33,6	25	17

**Specification**

- Zinc die casting  
Powder coated  
Black, textured finish
- Adjustable hand lever GN 302.1  
- Zinc die casting  
Powder coated  
Black, RAL 9005, textured finish  
- Threaded insert  
Stainless steel AISI 303 → Page 451
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166
- RoHS

**Information**

Clamping plates GN 953.7 are used in connection with position indicators GN 953 / GN 953.2. The mounting holes support typical bore hole patterns.

In a simpler manner and without great construction and installation effort these spindles can, after adjustment, be clamped and locked.

At the same time these plates are fitted with bore diameter 6.1 to accommodate the torque support of the position indicator.

The clamping plate can be installed so that the hand lever is situated as required either on the right or the left.

see also...

- Position Indicators GN 953 (Hollow Shaft Steel) → Page 396
- Position Indicators GN 953.2 (Hollow Shaft Stainless Steel) → Page QVX

How to order

**GN 953.7-48-B16**

- 1 b
- 2 d<sub>1</sub>

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

