


3 Type

- A Shaft-Ø $d_2 <$ Bore-Ø d_3
- B Shaft-Ø $d_2 =$ Bore-Ø d_3



1

2

d ₁	d ₂ H9 Bore of the control knob = Shaft Ø						d ₃ Bore Ø of the position indicator	d ₄ Bore Ø of the position indicator	l ₁	l ₂ Length of the protruding shaft		For position indicators
	Type A			type B						min.	max.	
22	B 6	B 8	-	-	-	B 10	10	M 4	15,5	4,5	9,6	GN 955 / GN 955.2
27	B 6	B 8	B 10	B 12	-	B 14	14	M 5	19,5	6	11,3	GN 954 / GN 954.2 / GN 9054 / GN 9154
42	B 10	B 12	B 14	B 15	B 16	B 20	20	M 6	24	6,5	15	GN 953 / GN 953.2 / GN 9053 / GN 9153

Specification

Knob

Aluminum
Anodized, black

Grub screw DIN 916

Stainless Steel
with internal hex and serrated point

Cover

Plastic, light gray

RoHS

Control knobs GN 957 are used in connection with position indicators. These control knobs offer a simple solution when the assembly requires manual fine adjustment for the application for which it has been designed. The design of this knob adapts it to the diameter of the adjustment shaft, so that no adapter bushings GN 952.1 are needed.

see also...

Page

- GN 953 | GN 953.2 Position Indicators (Hollow shaft steel / stainless steel) QVX / QVX
- GN 954 | GN 954.2 Position Indicators (Hollow shaft steel / stainless steel) QVX / QVX
- GN 955 | GN 955.2 Position Indicators (Hollow shaft steel / stainless steel) QVX / QVX
- GN 9053 | GN 9054 Position Indicators (Electronic) QVX / QVX
- GN 9153 | GN 9154 Position Indicators (Data Transmission via Radio Frequency) QVX / QVX

Technical Information

ISO Fundamental Tolerances

QVX

How to order

GN 957-27-B8-A

- 1 d₁
- 2 d₂
- 3 Type