



**3 Type**

- K** Straight lever with plain bore
- M** Straight lever with threaded bore
- L** Angled lever with plain bore
- N** Angled lever with threaded bore

1 2 2

Steel											
l <sub>1</sub>	d <sub>1</sub> Thread		d <sub>2</sub> H7 Bore		b	d <sub>3</sub>	d <sub>4</sub> ≈	d <sub>5</sub> -0,2	h ≈	l <sub>2</sub> ≈	
	Type M	Type N	Type K	Type L							
50	M 6	M 6	B 6	B 6	9,5	8	7,5	12	24	48	
63	M 8	M 8	B 8	B 8	12	10	11	16	30,5	60	
80	M 10	M 10	B 10	B 10	14,5	13	15	20	38	76	
100	M 12	M 12	B 12	B 12	18,5	16	19	25	47	95	
125	M 16	M 16	B 16	B 16	24	20	23,5	32	59,5	119	
160	M 20	M 20	B 20	B 20	30	25	29,5	40	76	152	
200	-	M 24	-	B 24	40	32	33	50	97	190	

1 2 2

Stainless steel									
l <sub>1</sub>	d <sub>1</sub> Thread	d <sub>2</sub> H7 Bore	b	d <sub>3</sub>	d <sub>4</sub> ≈	d <sub>5</sub> -0,2	h ≈	l <sub>2</sub> ≈	
	Type N	Type L							
50	M 6	-	9,5	8	7,5	12	24	48	
63	M 8	B 8	12	10	11	16	30,5	60	
80	M 10	B 10	14,5	13	15	20	38	76	
100	M 12	B 12	18,5	16	19	25	47	95	
125	M 16	-	24	20	23,5	32	59,5	119	

**Specification**

- Steel —
- Turned
- Blackened
- Stainless steel AISI 303 **NI**
- Matte shot blasted
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166
- RoHS

**On request**

- Stainless steel clamping levers with straight lever

**Hinweis**

The official DIN standard sheet specifies additional sizes 40 - M5 / B5.

see also...

- Clamp Nuts GN 99.5 (Steel) → Page 506
- Stainless Steel Clamp Nuts GN 99.6 → Page 506
- Adjustable Clamping Levers GN 99.2 → Page 490

How to order (Steel)	1 l <sub>1</sub>
<b>DIN 99-100-M12-N</b>	2 d <sub>1</sub> (d <sub>2</sub> )
	3 Type

How to order (Stainless steel)	1 l <sub>1</sub>
<b>DIN 99-63-M8-N-NI</b>	2 d <sub>1</sub> (d <sub>2</sub> )
	3 Type
	4 Material