



¹ s ₁	² s ₂	w	l ₁	l ₂
R 20	10	0,8 ... 2	3	12
R 20	15	1 ... 2	5	11,5
R 25	10	0,8 ... 2	3	11,5
R 25	15	1 ... 2,5	5	11,5
R 25	20	1 ... 3	5	11,5
R 30	10	1 ... 2	5	11,5
R 30	15	1 ... 2,5	5	11,5
R 30	20	1 ... 3	5	11,5
R 35	20	1 ... 2,5	5	11,5
R 35	25	1 ... 3	5	11,5
R 40	15	1 ... 2	5	12
R 40	20	1 ... 3	5	12
R 40	25	1 ... 3	5	11,5
R 40	30	1 ... 3	5	11
R 45	15	1,5 ... 2	5	11
R 45	20	1 ... 3	5	11,5
R 45	25	1 ... 3	5	12
R 50	20	1 ... 3	5	15

¹ s ₁	² s ₂	w	l ₁	l ₂
R 50	25	1 ... 3	5	11,5
R 50	30	1 ... 3	5	12
R 50	35	1 ... 3,5	5	14,5
R 50	40	1,5 ... 3	5	15
R 60	20	1 ... 3	5	14,5
R 60	30	1 ... 2,5	5	15
R 60	40	1 ... 3	5	14
R 60	50	1,5 ... 3,5	5	14,5
R 70	30	1 ... 3	5	15
R 70	40	1,5 ... 3	5	20
R 80	20	1 ... 3	5	18
R 80	30	1 ... 2,5	5	14,5
R 80	40	1 ... 3	5	14,5
R 80	50	1,5 ... 4	5	22
R 80	60	1,5 ... 3,5	5	25
R 100	40	1,5 ... 4	5	14,5
R 100	50	1,5 ... 4,5	5	24

Specification

- Plastic Technopolymer (Polyethylen PE)
 - Black, RAL 9005, matte finish **SW**
 - Grey, RAL 7042, matte finish **GR**
- *Plastic Characteristics* → Page 2158
- **RoHS**

On request

- Other sizes
- White, RAL 9003, matte finish **WS**



Information

Tube end plugs GN 991 have been designed for sealing tube ends for safety or optical reasons.

They are pressed into the tube end either by hand or with a mallet.

see also...

- *Construction Tubes GN 990* → Page 1835
- *Retaining Tubes / Retaining Rods GN 480.1* → Page 1833
- *Insert Bushings GN 992 (Aluminum, with Internal Thread)* → Page 1501

How to order

GN 991-R25-20-SW

¹	s ₁
²	s ₂
³	Color

