



4 Type
M Straight lever
N Angled lever

1 **2** **3**

d ₁	d ₂	l ₁	d ₃	d ₄	h ₁	h ₂	h ₃ ≈	l ₂	l ₃ ≈					
10	M 8	20	25	32	40	50	63	13,5	20	25	8	39,5	63	60
13	M 10	20	25	32	40	50	63	16	25	29	8	49,5	80	76
16	M 12	25	32	40	50	63	80	19	28	33,5	10,5	60,5	100	95

Specification

- Steel
 Blackened
 Threaded stud
 Property class 5.8
- *Strength Values of Screws* → Page 2152
- RoHS

Information

Adjustable clamping levers GN 99.2 are known for their small dimensions. They are for use in applications where either the clamping range is limited or where a specific lever position is required. The serrated bore in the spherical hub is fitted with a threaded bolt insert which engages in the hub with its own serrations. By depressing the clamping lever the serrations are disengaged freeing it for re-positioning in the most convenient position. When releasing the lever the serrations will re-engage automatically. Should a rotation of 360° not be possible the insert can be slightly screwed in (after the lever has been disengaged) by means of the slotted knurled screw.

How to order		1	d ₁
		2	d ₂
		3	l ₁
		4	Type
GN 99.2-13-M10-40-N			

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

