

Wheels and Casters

Overview of Casters

Standard		Coding	Wheel Ø in mm	Max. dynamic load capacity in N	Bracket type			Mounting methods		
					Rigid	Swi- vel	Swivel with total lock brake	Mounting plate	Center hole	Threa- ded stud
GN 22870 Page XYZ		L	40...80	300...550	x	x	x	x	x	x
GN 22870 Page XYZ		D	50...75	600...800	-	x	-	x	x	x
GN 22880 Page XYZ		L	40...60	400...700	x	x	x	x	x	x
GN 22880 Page XYZ		D	50	1400	-	x	-	x	x	x
GN 22872 Page XYZ		L	80...150	700...1800	x	x	x	x	x	-
GN 22873 Page XYZ		L	80...200	650...2250	x	x	x	x	x	-
GN 22874 Page XYZ		L	80...200	650...2300	x	x	x	x	x	-
GN 22875 Page XYZ		M	100...200	1800...5000	x	x	x	x	-	-
GN 22882 Page XYZ		L	80...200	1200...3000	x	x	x	x	x	-
GN 22882 Page XYZ		L	80...125	1200...2200	-	x	-	x	-	-
GN 22884 Page XYZ		L	80...200	750...3000	x	x	x	x	x	-
GN 22885 Page XYZ		L	80...200	2000...3000	x	x	x	x	x	-

L = Light version D = Double wheel version M = Medium version

Wheels and Casters

Overview of Casters

Standard		Coding	Wheel Ø in mm	Max. dynamic load capacity in N	Bracket type			Mounting methods		
					Rigid	Swivel	Swivel with total lock brake	Mounting plate	Center hole	Threa- ded stud
GN 22885 Page XYZ		M	125...200	3500...7500	x	x	x	x	-	-
GN 22886 Page XYZ		L	100...125	2000...2200	x	x	x	x	-	-
GN 22886 Page XYZ		M	100...200	3000...7000	x	x	x	x	-	-
GN 22887 Page XYZ		M	100...200	3500...7500	x	x	x	x	-	-
GN 22892 Page XYZ		L	65...200	1200...3000	x	x	x	x	x	-
GN 22892 Page XYZ		L	80...125	1800...2200	-	x	-	x	-	-
GN 22892 Page XYZ		M	100...200	3000...7300	x	x	x	x	-	-
GN 22894 Page XYZ		L	80...100	1500...2000	-	x	-	x	x	-
GN 22886 Page XYZ		H	160...200	5500...7000	x	x	x	x	-	-
GN 22887 Page XYZ		H	125...200	5500...10000	x	x	x	x	-	-
GN 22887 Page XYZ		E	150...300	10000...23000	x	x	x	x	-	-
GN 22892 Page XYZ		H	125...200	6500...9000	x	x	x	x	-	-

L = Light version M = Medium version H = Heavy version E = Extra-heavy version

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

