














































Latches

Types

Standard	Latch arm type	Housing form	Activation methods
GN 115 Page 1200 / 1202 / 1203 Latches Zinc die casting, Housing collar chrome-plated or black powder coated, Latch arm steel			  
GN 115.9 Page 1204 / 1205 Latches with safety function Housing collar black powder coated, Latch arm steel			 
GN 115 Page 1206 / 1207 / 1208 Latches Stainless steel  Inox Stainless Steel			  
GN 115 Page 1209 Latches Stainless steel (AISI 304 / AISI 316), protection class IP 69k  Inox Stainless Steel			
GN 515 Page XYZ / XYZ Latches with extended housing Zinc die casting, Housing collar black powder coated, Latch arm steel			  
GN 515 Page XYZ / XYZ Latches with extended housing Stainless steel  Inox Stainless Steel			

Standard		Latch arm type	Housing form	Activation methods
GN 1150 Page XYZ Latches Stainless steel, operating side in Hygienic Design    				
GN 1150 Page XYZ Latches Stainless steel, Operating and latch arm side in Hygienic Design    				
GN 115.1 Page 1210 Latches Zinc die casting, small type, Housing collar chrome-plated or black powder coated, Latch arm steel				
GN 115.6 Page 1212 Latches Stainless steel, small type  				
GN 115.3 Page 1214 Latches Plastic				
GN 115.5 Page 1216 Latches Plastic, Snap-in mounting				

3.1

3.2

3.3

3.4

3.5

3.6

3.7

3.8

3.9














Standard		Latch arm type	Housing form	Activation methods
GN 217 Page 1218 Latches Plastic, Latch arm steel				
GN 623.1 Page 1220 Latches Plastic, Latch arm steel				
GN 115.7 Page 1222 Latches with cabinet U-Handle Zinc die casting, Latch arm steel				
GN 115.10 Page 1224 / 1226 Latches with gripping tray Zinc die casting / Plastic, Latch arm steel, Clamp-mounted				
GN 731.2 Page 1228 Latches with gripping tray Plastic, Latch arm steel, Snap-in mounting				
GN 731.5 Page XYZ Latches with gripping tray Plastic, Latch arm stainless steel				



Inox
Stainless
Steel

Latches

Types

Standard		Latch arm type	Housing form	Activation methods
GN 116.1 Page 1230 Rotary clamping latches Zinc die casting, Housing collar black powder coated, Latch arm steel				
GN 516 Page 1232 Rotary clamping latches Zinc die casting, Housing collar black powder coated, Latch arm steel				
GN 516.5 Page 1234 Rotary clamping latches Stainless steel				
GN 516.1 Page 1235 Rotary clamping latches Zinc die casting, Housing collar black powder coated, Adjustable latch arm Zinc die casting				
GN 5630 Page 1236 Rotary Toggle Latches Plastic, Zinc die casting				
GN 117 Page 1238 Latches Steel				

3.1

3.2

3.3

3.4

3.5




















3.6

3.7

3.8

3.9



Standard		Latch arm type	Housing form	Activation methods
GN 119 Page 1240 Latches Zinc die casting, chrome-plated, Cam latch steel		 210°		
GN 119 Page 1242 Latches Stainless steel 		 210°		
GN 118 Page 1244 Latches Steel, sintered steel		 210°		
GN 119.3 Page 1246 Latches with cabinet U-handle Zinc die casting, black or silver powder coated, Cam latch steel		 210°		
GN 115.8 Page 1248 / 1250 / 1251 Hook-type latches Zinc die casting, Housing collar chrome-plated or black powder coated, Hook latch Steel, zinc plated		 90°	