



Highlights

Gears and Racks Made of Polyamid



Standard Parts. **Ganter.**

Content

Gears and Racks


General Notes	1
Technical Instructions	2
Technical Instructions for Plastic Gears	4
<hr/>	
Spur Gears GN 7802	6
Racks GN 7822	16

With the publication of this catalogue, all previous issues become invalid. Technical details are subject to change without notice. The details given herein comply with state of the art engineering at the time of printing. We reserve the right to amend errors and to remove individual articles from the product assortment. The products listed in this catalogue have been developed as standard products with the aim of covering the widest possible spectrum of requirements. We cannot be held liable and responsible for special applications involving extraordinary or unusual uses or requirements concerning our products. Our design department will be pleased to answer questions on certain product properties such as missing tolerance, dimensional details or strength classes. All rights in the catalogue are held by Otto Ganter GmbH & Co. KG. Reprints, also in extracts, are not permitted.
Otto Ganter GmbH & Co. KG, September 2022

Gears

Gears transfer a rotary motion from a driving shaft to a driven shaft via a positive locking. Depending on the ratio of the number of teeth of the gears used, the speed and the torque may be retained, decreased or increased. This is called the gear ratio, where the driven gear is put into relation with the driving gear. The reverse relationship applies to the resulting speeds. See the equations below. Due to the positive locking between the gear pairs, the rotational movement is transmitted precisely and without slippage.

A pairing of two or more combined gears is called a gear train or gearbox. The smallest gear is often referred to as the pinion, while the largest is simply called a gear. The driving and the driven gears always rotate in opposite directions. If this is not desired, a third gear must be positioned between them as an idler gear. Gear trains require only small center distances, which can be influenced by the number of teeth selected.



Gear ratio $i =$	
Speed ratio	$i = \frac{n_1}{n_2}$
Tooth count ratio	$i = \frac{z_2}{z_1}$


The tooth shape, size and geometry can be described based on a trapezoidal reference profile, which corresponds in principle to the profile of a rack. The tooth or trapezoid height is standardized with a module value, which is specified in millimeters. The angle of the symmetrical trapezoid sides is referred to as the pressure angle.

The reference profile is mapped onto the individual tooth by rolling over an involute curve along the contact surface. It is only possible to pair gears with the same module and pressure angle.

Racks

A rack can be considered a segment of a gear with an infinitely large diameter. The teeth of the rack then correspond precisely to the reference profile and have no bent tooth flanks. A combination of a rack and a spur gear allows rotational movements to be converted into linear movements or vice versa. The gear that engages with the rack is called a pinion. Rack drives are used in automation applications with high repeatable precision and frequent changes of direction and load.

Rack drives in which the rack remains stationary while the pinion moves along the rack are frequently used in conveyor systems. The reverse case, in which the pinion rotates around a fixed axis while the rack moves, is often used in extrusion systems as well as lifting and forward feed applications.




The most important mechanical value for the toothed racks is the maximum force that can be exerted on an individual tooth.


Gear Calculation

The following are the generally applicable formulas for the design of spur gears.

Formulas



Module m in mm	$m = \frac{p}{\pi}$	Pitch p in mm	$p = \pi \cdot m$
Tooth count z	$z = \frac{d}{m} = \frac{d_a - 2 \cdot m}{m}$	Tooth height h in mm	$h = 2 \cdot m + c$
Pitch circle Ø d in mm	$d = m \cdot z$	Addendum ha in mm	$h_a = m$
Addendum circle Ø da in mm	$d_a = d + 2 \cdot m = m \cdot (z + 2)$	Dedendum hf in mm	$h_f = m + c$
Root circle Ø df in mm	$d_f = d - 2 \cdot (m + c)$	Crest clearance c in mm	$c = 0,1 \cdot m \dots 0,3 \cdot m$



Gear ratio i	$i = \frac{z_2}{z_1} = \frac{n_1}{n_2}$
Reference center distance ad in mm	$a_d = \frac{d_1 + d_2}{2} = \frac{m \cdot (z_1 + z_2)}{2}$
Center distance a in mm	$a = \frac{d_1 + d_2}{2} + t$

The following tolerances **t** must be taken into account for the center distance **a**:

$t = +0,03 / +0,1$ with module 0,5 / 1 / 1,5


$t = +0,08 / +0,3$ with module 2 / 2,5 / 3

Tooth Profile

The spur gears GN 7802 have involute toothings with a pressure angle of 20°. Only gears with the same module and pressure angle can be paired with each other.

The following relationship applies to the involute toothings:

Involute Toothings




The tooth flanks of the gears are shaped as involutes.

The tangent that is perpendicular to the line of action runs through the contact point between the two tooth flanks (involute). The line of action is at a 20° angle to the pitch line of engagement.

The pitch point is located on the line of engagement at the intersection between the line of action and the center line of the gear axes.

For each gear, a counter gear with an infinitely large pitch diameter can be designed, which has a trapezoidal tooth profile. This reference profile then corresponds precisely to the profile of the rack.



Base circle diameter d_b	$d_b = d \cdot \cos \alpha = z \cdot m \cdot \cos \alpha$	The pitch p on the pitch circle corresponds to the pitch p on the line of engagement.
Base pitch p_b	$p_b = \frac{d_b \cdot \pi}{z} = p \cdot \cos \alpha$	The base pitch p_b corresponds to the contact pitch p_e .
Contact pitch p_e	$p_e \triangleq p_b = p \cdot \cos \alpha = \pi \cdot m \cdot \cos \alpha$	The contact pitch p_e is determined by the pitch p and the size of the pressure angle α .

Material-specific Advantages

The gears GN 7802 are made of polyamide and offer the following material-specific advantages:

- Weight reduction compared with metal gears
- Noise reduction
- Low coefficient of friction, meaning that lubrication is not absolutely required
- High corrosion resistance
- Higher torque transmission compared with other plastics, such as polyacetal (POM) / polyketone (PK)

In addition, gears of steel are frequently overdimensioned for their application. In such cases, polyamide gears are a cost-effective alternative. The spur gears GN 7802 of polyamide are frequently used in the following applications:

- Packaging and conveyor machines
- Industrial cleaning machines
- Glass and ceramic processing machines
- Agricultural machinery
- Chemical and pharmaceutical industry
- Household appliances

Lubrication / Maintenance

One of the main advantages of the spur gears GN 7802 of plastic is the possibility of using them without lubrication. If lubrication is still required to decrease friction and wear or to increase the lifespan of the gear, lithium-saponified grease with a mineral oil base is recommended.

Gear Pairing – Metal and Plastic

The spur gears GN 7802 of plastic can also be used in combination with metal gears.

With this pairing, the smallest gear (pinion) should be of metal and the larger gear of plastic since the wear on the larger gear is distributed over more teeth, resulting in a longer lifespan.

The combination of metal and plastic gears offers additional advantages since metal has a higher thermal conductivity, leading to better heat dissipation during operation and an associated decrease in wear on the plastic gear.

Hub Machining of Plastic Gears

The following points must be observed when making a bore or keyway:

- The clamping jaws used must be precisely matched to the addendum circle of the gear.
- The clamping surface must be as wide as possible. For module 3, for example, it is necessary to clamp at least 3 - 4 teeth and for module 1 at least 7 teeth.
- Cutting parameters and forward feed rates suitable for polyamide must be selected based on the machining method. Cooling or lubrication must be used during machining, if necessary.


Torque

The torque specifications in the table of the respective standard sheet have been determined through a combination of theoretical calculations and laboratory tests. The empirically determined data has been verified with suitable software, taking into account the VDI 2736 guideline for the design of thermoplastic gears.

The test series were carried out in continuous operation at a speed of 100-150 rpm without lubrication in order to test the most severe conditions.

The following assumptions were used for the theoretical calculation:




- The tooth force F is decomposed into the tangential force F_t and radial force F_r .
- The radial force F_r is considered negligible. As a result, the tooth force F can be simply assumed to have the same value as the tangential force F_t on the pitch circle.
- The least favorable case is assumed, in which only one tooth is engaged.



The tangential force F_t is then correlated with the torque via the pitch circle diameter. The following formula applies to the nominal torque:

$$M = F_t \cdot \frac{d}{2}$$

The torques given in the standard sheet should be considered guide values and may vary based on the specific application situation. Operating conditions such as speed, temperature, pairing of gears of different materials, lubricated or dry operation, etc. have a major influence on the load capacity.



1

2

Module	z Tooth count	b ₁ Tooth width	b ₂	d ₁	d ₂ Pitch circle Ø	d ₃	d ₄ Pre-bored hole	Max. torque in Nm
0,5	24	8	16	13	12	10	-	0,7
0,5	25	8	16	13,5	12,5	10	-	0,7
0,5	30	8	16	16	15	10	-	0,8
0,5	32	8	16	17	16	10	-	0,9
0,5	36	8	16	19	18	10	-	1
0,5	40	8	16	21	20	10	-	1,1
0,5	45	8	16	23,5	22,5	10	-	1,2
0,5	48	8	16	25	24	10	-	1,3
0,5	50	8	16	26	25	10	-	1,4
0,5	55	8	16	28,5	27,5	20	4	1,5
0,5	60	8	16	31	30	20	4	1,6
0,5	70	8	16	36	35	20	4	1,9
0,5	80	8	16	41	40	20	4	2,2

Specification

- Plastic Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 120 °C
 - Gray 
- ISO Fundamental Tolerances → Page 2151
- Plastic Characteristics → Page 2158
- RoHS

On request

- With keyway
- With bore H9

3

Information

Spur gears GN 7802 of plastic reduce both weight and noise while offering high corrosion resistance.

Spur gears of polyamide allow the transmission of significantly higher torques compared with gears made of other plastics. This makes them especially suited for applications with high torques at low speeds.

The spur gears have involute toothing with a pressure angle of 20°. Further design details can be found in the technical information.

see also...

- General Notes for Gears → Page 1
- Technical Instructions for Gears → Page 2


How to order

GN 7802-0,5-30-GR

1	Module
2	Tooth count z
3	Color





Spur Gears GN 7802
Gear Racks GN 7822 → *Page 16*



elesa
Original design ZCL



Application example



Gear rack GN 7822



Module	z Tooth count		b ₁ Tooth width	b ₂	d ₁	d ₂ Pitch circle Ø	d ₃	d ₄ Pre-bored hole	d ₅	Max. torque in Nm
	GR	VDB								
1	12	12	15	25	14	12	9	4	-	2,5
1	14	-	15	25	16	14	10	4	-	2,9
1	15	15	15	25	17	15	10	4	-	3,1
1	16	16	15	25	18	16	13	5	-	3,3
1	18	-	15	25	20	18	14	5	-	3,7
1	20	20	15	25	22	20	16	5	-	4,1
1	21	-	15	25	23	21	16	5	-	4,3
1	22	-	15	25	24	22	18	5	-	4,5
1	24	24	15	25	26	24	20	6	-	4,9
1	25	-	15	25	27	25	20	6	-	5,1
1	26	-	15	25	28	26	22	6	-	5,3
1	27	-	15	25	29	27	22	6	-	5,5
1	28	-	15	25	30	28	22	6	-	5,7
1	30	30	15	25	32	30	25	6	-	6,1
1	32	32	15	25	34	32	25	6	-	6,6
1	33	-	15	25	35	33	25	6	-	6,8
1	34	-	15	25	36	34	30	8	-	7,0
1	35	-	15	25	37	35	30	8	-	7,2

Module	z Tooth count		b ₁ Tooth width	b ₂	d ₁	d ₂ Pitch circle Ø	d ₃	d ₄ Pre-bored hole	d ₅	Max. torque in Nm
	GR	VDB								
1	36	36	15	25	38	36	30	8	-	7,4
1	38	-	15	25	40	38	30	8	-	7,8
1	39	-	15	25	41	39	30	8	-	8,0
1	40	40	15	25	42	40	30	8	-	8,2
1	42	-	15	25	44	42	35	10	-	8,6
1	44	-	15	25	46	44	35	10	-	9
1	45	45	15	25	47	45	35	10	-	9,2
1	48	48	15	25	50	48	35	10	-	9,8
1	50	-	15	25	52	50	35	10	-	10,2
1	55	-	15	25	57	55	35	14	44	11,3
1	58	-	15	25	60	58	35	14	44	11,9
1	60	60	15	25	62	60	40	14	51	12,3
1	65	-	15	25	67	65	40	20	51	13,3
1	70	-	15	25	72	70	40	20	61	14,3
1	72	-	15	25	74	72	40	20	61	14,7
1	74	-	15	25	76	74	40	20	61	15,2
1	75	-	15	25	77	75	50	20	66	15,4
1	77	-	15	25	79	77	50	20	66	15,8
1	80	-	15	25	82	80	50	20	66	16,4

Specification

- Plastic Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 120 °C
 - Gray 
- Plastic Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 120 °C
 - FDA compliant plastic granulate
 - Blue, RAL 5005, matte finish
 - Visually detectable 
- ISO Fundamental Tolerances → Page 2151
- Plastic Characteristics → Page 2158
- RoHS

On request

- With keyway
- With bore H9

Information

Spur gears GN 7802 of plastic reduce both weight and noise while offering high corrosion resistance.

Spur gears of polyamide allow the transmission of significantly higher torques compared with gears made of other plastics. This makes them especially suited for applications with high torques at low speeds.

The spur gears have involute toothing with a pressure angle of 20°. Further design details can be found in the technical information.


see also...

- General Notes for Gears → Page 1
- Technical Instructions for Gears → Page 2
- Product Family Standard Parts made of Detectable Plastics → Page 2157


How to order

GN 7802-1-30-GR



1	Module
2	Tooth count z
3	Color



$z \geq 38$



Application example



Gear rack GN 7822



1

2

Module	z Tooth count		b ₁ Tooth width	b ₂	d ₁	d ₂ Pitch circle Ø	d ₃	d ₄ Pre-bored hole	d ₅	Max. torque in Nm
	GR	VDB								
1,5	12	12	17	30	21	18	14	5	-	6,8
1,5	14	-	17	30	24	21	16	5	-	8
1,5	15	15	17	30	25,5	22,5	18	5	-	8,5
1,5	16	-	17	30	27	24	18	5	-	9,1
1,5	18	18	17	30	30	27	20	6	-	10,3
1,5	20	20	17	30	33	30	25	8	-	11,4
1,5	21	-	17	30	34,5	31,5	25	8	-	12
1,5	22	-	17	30	36	33	28	8	-	12,5
1,5	24	24	17	30	39	36	28	8	-	13,7
1,5	25	-	17	30	40,5	37,5	30	8	-	14,2
1,5	26	-	17	30	42	39	30	8	-	14,8
1,5	28	-	17	30	45	42	30	8	-	16
1,5	30	30	17	30	48	45	35	12	-	17,1
1,5	32	-	17	30	51	48	35	12	-	18,2
1,5	33	-	17	30	52,5	49,5	35	12	-	18,8
1,5	34	-	17	30	54	51	35	12	-	19,4
1,5	35	-	17	30	55,5	52,5	35	12	-	19,9
1,5	36	36	17	30	57	54	35	12	-	20,5

Module	z		b ₁ Tooth width	b ₂	d ₁	d ₂ Pitch circle Ø	d ₃	d ₄ Pre-bored hole	d ₅	Max. torque in Nm
	Tooth count GR	VDB								
1,5	38	-	17	30	60	57	35	16	42	21,7
1,5	39	-	17	30	61,5	58,5	35	16	42	22,2
1,5	40	40	17	30	63	60	40	16	48	22,8
1,5	42	-	17	30	66	63	45	16	53	23,9
1,5	44	-	17	30	69	66	45	16	53	25,1
1,5	45	-	17	30	70,5	67,5	45	16	53	25,6
1,5	46	-	17	30	72	69	45	16	53	26,2
1,5	48	48	17	30	75	72	45	16	53	27,4
1,5	50	-	17	30	78	75	45	16	53	28,5
1,5	51	-	17	30	79,5	76,5	50	20	63	29,1
1,5	52	-	17	30	81	78	50	20	63	29,6
1,5	54	-	17	30	84	81	50	20	63	30,8
1,5	55	-	17	30	85,5	82,5	50	20	63	31,3
1,5	60	-	17	30	93	90	55	20	73	34,2
1,5	65	-	17	30	100,5	97,5	60	20	81	37
1,5	70	-	17	30	108	105	60	20	93	39,9
1,5	75	-	17	30	115,5	112,5	60	20	93	42,7
1,5	80	-	17	30	123	120	60	20	109	45,6

Specification

- Plastic Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 120 °C
 - Gray 
- Plastic Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 120 °C
 - FDA compliant plastic granulate
 - Blue, RAL 5005, matte finish
 - Visually detectable 
- ISO Fundamental Tolerances → Page 2151
- Plastic Characteristics → Page 2158
- RoHS

On request

- With keyway
- With bore H9

Information

Spur gears GN 7802 of plastic reduce both weight and noise while offering high corrosion resistance.

Spur gears of polyamide allow the transmission of significantly higher torques compared with gears made of other plastics. This makes them especially suited for applications with high torques at low speeds.

The spur gears have involute toothing with a pressure angle of 20°. Further design details can be found in the technical information.



see also...

- General Notes for Gears → Page 1
- Technical Instructions for Gears → Page 2
- Product Family Standard Parts made of Detectable Plastics → Page 2157



How to order

GN 7802-1,5-48-VDB

1	Module
2	Tooth count z
3	Color



Application example



Gear rack GN 7822



Module	z Tooth count		b ₁ Tooth width	b ₂	d ₁	d ₂ Pitch circle Ø	d ₃	d ₄ Pre-bored hole	d ₅	Max. torque in Nm
	GR	VDB								
2	12	12	20	35	28	24	18	8	-	15,5
2	13	-	20	35	30	26	18	8	-	16,8
2	14	-	20	35	32	28	20	8	-	18,1
2	15	15	20	35	34	30	22	8	-	19,4
2	16	-	20	35	36	32	25	8	-	20,7
2	17	-	20	35	38	34	25	8	-	21,9
2	18	-	20	35	40	36	30	10	-	23,2
2	19	-	20	35	42	38	30	10	-	24,5
2	20	20	20	35	44	40	30	10	-	25,8
2	21	-	20	35	46	42	30	10	-	27,1
2	22	-	20	35	48	44	30	10	-	28,4
2	23	-	20	35	50	46	35	10	-	29,7
2	24	24	20	35	52	48	35	10	-	31
2	25	-	20	35	54	50	35	10	-	32,3
2	26	-	20	35	56	52	40	14	-	33,6
2	27	-	20	35	58	54	40	14	-	34,9
2	28	-	20	35	60	56	40	14	-	36,1
2	29	-	20	35	62	58	40	14	-	37,4
2	30	30	20	35	64	60	40	14	-	38,7
2	31	-	20	35	66	62	40	14	48	40
2	32	-	20	35	68	64	45	16	51	41,3
2	33	-	20	35	70	66	45	16	51	42,6
2	34	-	20	35	72	68	45	16	51	43,9
2	35	-	20	35	74	70	45	16	51	45,2
2	36	36	20	35	76	72	50	16	59	46,5
2	37	-	20	35	78	74	50	16	59	47,8
2	38	-	20	35	80	76	50	16	59	49,1

Module	z Tooth count		b ₁ Tooth width	b ₂	d ₁	d ₂ Pitch circle Ø	d ₃	d ₄ Pre-bored hole	d ₅	Max. torque in Nm
	GR	VDB								
2	39	-	20	35	82	78	50	16	59	50,4
2	40	40	20	35	84	80	55	16	66	51,6
2	42	-	20	35	88	84	55	16	66	54,2
2	44	-	20	35	92	88	60	16	68	56,8
2	45	-	20	35	94	90	60	16	68	58,1
2	46	-	20	35	96	92	60	16	75	59,4
2	48	48	20	35	100	96	60	16	75	62
2	50	-	20	35	104	100	60	20	84	64,6
2	52	-	20	35	108	104	60	20	90	67,1
2	54	-	20	35	112	108	60	20	90	69,7
2	57	-	20	35	118	114	60	20	90	73,6
2	60	-	20	35	124	120	60	20	101	77,5
2	62	-	20	35	128	124	60	20	101	80
2	64	-	20	35	132	128	60	20	101	82,6
2	65	-	20	35	134	130	60	20	101	83,9
2	66	-	20	35	136	132	60	20	101	85,2
2	68	-	20	35	140	136	60	20	101	87,8
2	70	-	20	35	144	140	60	20	117	90,4
2	72	-	20	35	148	144	60	20	117	93
2	74	-	20	35	152	148	60	20	117	95,5
2	75	-	20	35	154	150	60	20	117	96,8
2	76	-	20	35	156	152	60	20	117	98,1
2	78	-	20	35	160	156	60	20	117	100,7
2	80	-	20	35	164	160	60	20	117	103,3
2	90	-	20	35	184	180	60	20	147	116,2
2	100	-	20	35	204	200	60	25	183	129,1

Specification

- Plastic Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 120 °C
 - Gray 
- Plastic Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 120 °C
 - FDA compliant plastic granulate
 - Blue, RAL 5005, matte finish
 - Visually detectable 
- ISO Fundamental Tolerances → Page 2151
- Plastic Characteristics → Page 2158
- RoHS

On request

- With keyway
- With bore H9

Information

Spur gears GN 7802 of plastic reduce both weight and noise while offering high corrosion resistance.

Spur gears of polyamide allow the transmission of significantly higher torques compared with gears made of other plastics. This makes them especially suited for applications with high torques at low speeds.

The spur gears have involute toothing with a pressure angle of 20°. Further design details can be found in the technical information.


see also...

- General Notes for Gears → Page 1
- Technical Instructions for Gears → Page 2
- Product Family Standard Parts made of Detectable Plastics → Page 2157

How to order

GN 7802- 2-21-GR

1	Module
2	Tooth count z
3	Color



1 2

Module	z Tooth count	b ₁ Tooth width	b ₂	d ₁	d ₂ Pitch circle Ø	d ₃	d ₄ Pre-bored hole	d ₅	Max. torque in Nm
2,5	12	25	40	35	30	22	8	-	30,3
2,5	14	25	40	40	35	22	8	-	35,3
2,5	15	25	40	42,5	37,5	30	10	-	37,8
2,5	16	25	40	45	40	30	10	-	40,3
2,5	18	25	40	50	45	35	10	-	45,4
2,5	20	25	40	55	50	35	10	-	50,4
2,5	22	25	40	60	55	40	16	-	55,5
2,5	23	25	40	62,5	57,5	40	16	-	58
2,5	24	25	40	65	60	40	16	-	60,5
2,5	25	25	40	67,5	62,5	40	16	-	63
2,5	26	25	40	70	65	40	16	-	65,6
2,5	27	25	40	72,5	67,5	40	16	50	68,1
2,5	28	25	40	75	70	40	16	50	70,6
2,5	29	25	40	77,5	72,5	45	16	56	73,1
2,5	30	25	40	80	75	45	16	56	75,6
2,5	32	25	40	85	80	50	16	61	80,7
2,5	35	25	40	92,5	87,5	50	16	61	88,3
2,5	40	25	40	105	100	50	18	73	100,9
2,5	45	25	40	117,5	112,5	60	18	85	113,5
2,5	50	25	40	130	125	60	20	105	126,1

Specification

- Plastic Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 120 °C
 - Gray GR
- ISO Fundamental Tolerances → Page 2151
- Plastic Characteristics → Page 2158
- RoHS

On request

- With keyway
- With bore H9

3 **Information**

Spur gears GN 7802 of plastic reduce both weight and noise while offering high corrosion resistance.

Spur gears of polyamide allow the transmission of significantly higher torques compared with gears made of other plastics. This makes them especially suited for applications with high torques at low speeds.

The spur gears have involute toothing with a pressure angle of 20°. Further design details can be found in the technical information.


see also...

- General Notes for Gears → Page 1
- Technical Instructions for Gears → Page 2

How to order

1 2 3
GN 7802-2,5-45-GR

1	Module
2	Tooth count z
3	Color



1 2

Module	z Tooth count	b ₁ Tooth width	b ₂	d ₁	d ₂ Pitch circle Ø	d ₃	d ₄ Pre-bored hole	d ₅	Max. torque in Nm
3	12	30	45	42	36	25	12	-	52,3
3	14	30	45	48	42	30	12	-	61
3	15	30	45	51	45	30	12	-	65,4
3	16	30	45	54	48	35	12	-	69,7
3	18	30	45	60	54	40	12	-	78,4
3	20	30	45	66	60	45	12	-	87,1
3	22	30	45	72	66	45	16	-	95,9
3	23	30	45	75	69	45	16	-	100,2
3	24	30	45	78	72	45	16	-	104,6
3	25	30	45	81	75	45	16	-	108,9
3	26	30	45	84	78	45	16	-	113,3
3	27	30	45	87	81	45	16	-	117,6
3	28	30	45	90	84	50	16	65	122
3	29	30	45	93	87	50	16	65	126,4
3	30	30	45	96	90	50	16	65	130,7
3	32	30	45	102	96	50	16	73	139,4
3	35	30	45	111	105	60	20	80	152,5
3	40	30	45	126	120	60	20	85	174,3
3	45	30	45	141	135	60	20	101	196,1
3	50	30	45	156	150	60	20	127	217,6

Specification

- Plastic Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 120 °C
 - Gray GR
- ISO Fundamental Tolerances → Page 2151
- Plastic Characteristics → Page 2158
- RoHS

On request

- With keyway
- With bore H9

3

Information

Spur gears GN 7802 of plastic reduce both weight and noise while offering high corrosion resistance.

Spur gears of polyamide allow the transmission of significantly higher torques compared with gears made of other plastics. This makes them especially suited for applications with high torques at low speeds.

The spur gears have involute toothing with a pressure angle of 20°. Further design details can be found in the technical information.



see also...

- General Notes for Gears → Page 1
- Technical Instructions for Gears → Page 2


How to order

GN 7802-3-50-GR

1	Module
2	Tooth count z
3	Color



Application example



3 Type

VG Square, straight, toothed

1

2

Module	Length l		b Tooth width	h	s	Max. force F_S acting on a tooth in N
	Nominal size	Actual size				
1	350	352	15	15	8	372
1,5	250	250	17	17	8	633
1,5	500	565	17	17	8	633
2	250	251	20	20	10	993
2	500	565	20	20	10	993
3	250	254	30	30	15	2234
3	500	500	30	30	15	2234

Specification

4

- Plastic Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 120 °C
 - Gray ● GR
- *Plastic Characteristics* → Page 2158
- **RoHS**

On request

- Other types

Information

Gear racks GN 7822 are used in combination with spur gears GN 7802 to convert rotary motion into linear motion. They are used in automation applications with high repeatable precision and frequent changes of direction and load.

The steel core increases the stiffness and prevents bending of the racks. In addition, modules 1 / 1.5 / 2 are designed for continuous installation of the racks.

The gear racks have a reference profile toothing with a pressure angle of 20°. The force F_S refers to the maximum permissible force that can be applied to a single tooth.

see also...


- *General Notes for Gears* → Page 1
- *Technical Instructions for Gears* → Page 2

How to order

GN 7822-1,5-250-VG-GR

- 1** Module
- 2** Length l
- 3** Type
- 4** Color

**Over 60,000 Standard Parts.
2,200 Pages.
Easy. Comprehensive. Essential.
Request Now.**



Standard Parts Catalogue

Operating with Handles and Knobs · Operating by Using Machine and Device
Handles · Adjusting with Handwheels and Cranks · Adjusting, Positioning,
Locking with and without Position Indication · Tensioning, Clamping,
Switching with Levers · Tensioning, Clamping with Knobs · Tensioning with
Eccentric Cams and Wedge Clamps · Tensioning with Clamping Mechanisms
Indexing, Locking, Blocking with Pins and Ball-Shaped Elements · Mounting,
Positioning, Leveling with Screws, Clamping and Supporting Elements ·
Hinging, Latching, Locking of Doors and Covers · Installing, Lifting, Damping
with Leveling Feet, Lifting Gear and Rubber Elements · Controlling, Venting,
Sealing of Liquids and Gases · Moving, Transferring, Connecting with
Shafts and Joints · Connecting, Assembling with Clamping and Connecting
Elements · Adjusting, Moving with Guides, Spindles and Ball Rollers ·
Holding with Magnets

Operating with Handles and Knobs · Operating with Handwheels and Cranks · Adjusting, Positioning, Locking with and without Position Indication · Tensioning, Clamping, Switching with Levers · Tensioning, Clamping with Knobs · Tensioning with Eccentric Cams and Wedge Clamps · Tensioning with Clamping Mechanisms Indexing, Locking, Blocking with Pins and Ball-Shaped Elements · Mounting, Positioning, Leveling with Screws, Clamping and Supporting Elements · Hinging, Latching, Locking of Doors and Covers · Installing, Lifting, Damping with Leveling Feet, Lifting Gear and Rubber Elements · Controlling, Venting, Sealing of Liquids and Gases · Moving, Transferring, Connecting with Shafts and Joints · Connecting, Assembling with Clamping and Connecting Elements · Adjusting, Moving with Guides, Spindles and Ball Rollers · Holding with Magnets



Scan code and request the catalogue free of charge



Otto Ganter GmbH & Co. KG

Triberger Straße 3
78120 Furtwangen
Deutschland

Tel. +49 7723 6507-100

Mail info@ganternorm.com

www.ganternorm.com